




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW RELEASE PER ECO-14-013594	09-05-14	DM	DM




Backshell

Compression Nut



SECTION A-A

6. PART NO. M902-2162
5. CABLE STRIPPED LENGTH: 63.50 [2.500] MAX.
4. CABLE SIZE: Ø.300 - Ø.430
3. TEMPERATURE RATING: -40°C TO +134°C [-40°F TO +273°F]
2. THIS PART IS USED WITH:
COMPRESSION NUT, M902-2042
1. THIS PART IS USED ON
HD1X-6-96X PLUG / RECEPTACLES
HD1X-6-12X PLUG / RECEPTACLES
SEE INVIDUAL CUSTOMER DRAWINGS

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. MEYER 05SEP2014		TE Connectivity							
		CHK I. GRANTCHAROVA 05SEP2014									
DIMENSIONS: MM [INCH]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± .63 [.025] 3 PLC ± 4 PLC ± ANGLES ± 5°		NAME BACKSHELL, SIZE 6 CABLE SIZE: Ø.300 - Ø.430 HD10 SERIES							
				APVD D. MEYER 05SEP2014							
				PRODUCT SPEC							
				APPLICATION SPEC							
MATERIAL PC/PBT		FINISH BLACK		SIZE A 3		CAGE CODE 4AFU8		DRAWING NO M902-2162		RESTRICTED TO -	
				WEIGHT 13.98 g							
Customer Drawing						SCALE NONE		SHEET 1 OF 1		REV A	