




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW RELEASE PER ECO-14-013594	09-05-14	DM	DM




SECTION A-A



Backshell

Compression Nut

6. PART NO. M902-2164
5. CABLE STRIPPED LENGTH: 63.50 [2.500] MAX.
4. CABLE SIZE: Ø.570 - Ø.710
3. TEMPERATURE RATING: -40°C TO +134°C [-40°F TO +273°F]
2. THIS PART IS USED WITH:
COMPRESSION NUT, M902-2054
1. THIS PART IS USED ON
HD1X-6-96X PLUG / RECEPTACLES
HD1X-6-12X PLUG / RECEPTACLES
SEE INDIVIDUAL CUSTOMER DRAWINGS

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. MEYER 05SEP2014		 TE Connectivity			
		CHK I. GRANTCHAROVA 05SEP2014					
DIMENSIONS: MM [INCH]	0 PLC ± 1 PLC ± 2 PLC ± .63 [.025] 3 PLC ± 4 PLC ± ANGLES ± 5° 	APVD D. MEYER 05SEP2014		NAME BACKSHELL, SIZE 6 CABLE SIZE: Ø.570 - Ø.710 HD10 SERIES			
PRODUCT SPEC							
APPLICATION SPEC							
WEIGHT 18.64 g							
MATERIAL PC/PBT		FINISH BLACK	Customer Drawing		SIZE A 3	CAGE CODE 4AFU8	DRAWING NO C M902-2164