

ALL DIMENSIONS IN MM. DO NOT SCALE PRINT




PRINT DIST

AMP-J
REV. 10/83


METRIC

3rd ANGLE PROJECTION

NUMBER
C-176281



断面 "A-A"
(SECT)



注:

- 適用製品規格: 108-5302
- 適用コンタクト型番
タブ・コンタクト: 175150-□(*20-16AWG)
175149-□(*26-22AWG)
- 嵌合相手側製品型番
プラグ・ハウジング: 176270-□
リセ・コンタクト: 175152-□(*20-16AWG)
175151-□(*26-22AWG)
- 取扱説明書: 15-503J

5. APPLICATION SPEC.: 114-5142

NOTES:

- PRODUCT SPEC.: 108-5302
- APPLICABLE CONTACT P/N
TAB CONTACT: 175150-□(*20-16AWG)
175149-□(*26-22AWG)
- MATING CONN. P/N
PLUG HSG: 176270-□
REC CONTACT: 175152-□(*20-16AWG)
175151-□(*26-22AWG)
- INSTRUCTION SHEET: 15-503J

黒 (BLACK)	1	176281-9
青 (BLUE)	↑	↑ -6
黄 (YELLOW)		↑ -4
赤 (RED)	↓	↓ -2
自然色 (NATURAL)	1	176281-1
ハウジング色調 極数	型番	
(HOUSING COLOR) (Pos.)	(P/N)	

				AMP 日本エー・エム・ピー株式会社 Tokyo, Japan			
				名称 (NAME) AMPユニバーサル・パワー・コネクタ 1極 3.96mmピッチ キヤップ・ハウジング (1列タイプ) AMP UNIVERSAL POWER CONN. 3.96mm PITCH CAP HOUSING 1 Pos (SGL ROW)			
				一般公差 10mm以下: ±0.2 10mm以上: ±0.25 30mm以上: ±0.3 角 度: ±3°			
				SIZE LOC 番号 (No.) A3 J C-176281			
				尺度 (SCALE) REV. B SHEET 1 OF 1			
				(CUSTOMER DRAWING)			

B	REVISED PER ECR-19-017623	M.G	D.Z	DATE	材料 (MATERIAL) 6/6 ナイロン (UL94V-0) 6/6 NYLON (UL94V-0)	仕上 (FINISH)	DR. M. S. 1/20/88	DE. M. S. 1/20/88	CHK. Y. 1/20/88	APP. Y. 1/20/88
A1	ECR-19-017851	SM	DZ	2003/10/20						
A	数量 J-12715	MS	KS	1/2/89						
O	作成 J-12204	MS	KS	1/2/89						
LTR	変更 (REVISION RECORD)	DR	CHK	DATE						