



Die deutsche Version dieser Zeichnung dient nur zur Erleichterung der Handhabung der Zeichnungen von den englischen Original gilt als verbindlich. Alle Änderungen von den englischen Original gilt als Änderung. The german version of this drawing has been offered for convenience only and may deviate from the english original. In case of any deviation the English version shall prevail.

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patent-, Gebrauchsmuster- oder Geschmacksmustererregung vorbehalten. The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design.



X





X

Tauchlötanschluss 0,3 x 0,7mm
solder terminal 0,3 x 0,7 mm

Anforderungsstufe 2 = 400 Steckzyklen
performance class 2 = 400 mating cycles

Fehlende Maße und Angaben nach IEC 60 603-2 / DIN EN 60 603-2
Missing information and dimensions per IEC 60 603-2 / DIN EN 60 603-2



Dimension no.				Tolerances Dim. for Information ISO 8015		 All Dimensions in mm		Scale 2:1			
Customer drawing: THIS DRAWING IS A CONTROLLED DOCUMENT.				Subject to modification without prior notice. Drawing will not be updated.		ERNI-DIN 41612 / IEC-60603-2 Female Connector Q/3 20 Solder Type 7					
				 TE Connectivity		C-294927-E				I	
a		27.05.2021				Class				STVQ/3	
Index		Date								A3	