








TE Connectivity. All Rights Reserved.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	F	REVISED PER ECN-26-376948	23MAR2026	FZ	LL




NOTES

1. MATERIAL:HOUSING:GLASS FILED THERMO PLASTIC
,POLYESTER(94V-0),COLOR:BLACK
TAB CONTACT:COPPER ALLOY
RETENTION LEG:BRASS

2. FINISH(CONTACT AREA):0.38 μ m Min. PdNi & GOLD FLASH

3. FINISH(CONTACT AREA):0.76 μ m Min. PdNi & GOLD FLASH

4. FINISH(RETENTION LEG): TIN PLATED
(CONTACT TAIL) OVER NICKEL



推奨基板取付け穴寸法 <公差:±0.05>

PC 基板厚:1.6~2.4±0.1
(コネクタ搭載面)PC 基板厚:3.2±0.1
6-353080-2 ONLY

RECOMENDED PC BOARD HOLE PATTERN(TOL:±0.05)

PC BOARD THICKNESS:1.6~2.4±0.1
(CONNECTOR MOUNT SIDE)PC BOARD THICKNESS:3.2±0.1
6-353080-2 ONLY

Y	 	2-353080-3
	 	2-353080-2
X	 	1-353080-3
	 	6-353080-2
	 	1-353080-2
KEY TYPE	コンタクトのめっき (FINISH)	製品番号 (PART NO.)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± - 102 ±0.3 1 PLC ± - 302 >10:±0.35 2 PLC ± - 1002 >30:±0.4 3 PLC ± - 4 PLC ± - ANGLES ± 3° FINISH
MATERIAL SEE NOTE	SEE NOTE

DWN K.IKEDA 04JUL196	CHK Y.ISHIKAWA 04JU1996
APVD S.MANABE 04JUL1996	PRODUCT SPEC 108-5453
APPLICATION SPEC 114-5206	WEIGHT 0.000000
CUSTOMER DRAWING	

NAME SINGLE ROW HEADER ASSY 2P -V-TYPE DYNAMIC D-5200 S			
SIZE A3	CAGE CODE 00779	DRAWING NO C-353080	RESTRICTED TO -
SCALE 1:1		SHEET 1 OF 1	REV F