

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	12	ECN-25-356402	27OCT2025	GSK	AK


NOTES: -

1. CHARACTERS: -
- 0-9, A-Z, +, -, /,~, ≡
- 0, 1, 6 & 9 FOLLOWED BY A FULL STOP.
- HEIGHT 2.6 - 2.9 mm
- TOLERANCE (AXIAL) ±0.75
- (ROTATIONAL) ±5°


CHEVRON CUT MARKERS: -

CHARACTERS TO BE CENTRALLY DISPOSED ON MARKER FACE AND IN THE ATTITUDE SHOWN RELATIVE TO CHEVRON.

2. MARKER LENGTHS (DIMENSION 'A'):
- WITH SINGLE MARK 3.70 - 4.50
- WITH DOUBLE MARK 6.50 - 7.50



CHEVRON CUT



STRAIGHT CUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 11FEB2020 GOPALAKRISHNA H V	TE Connectivity		
		CHK 11FEB2020 ALAN KEAN			
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD 11FEB2020 ALAN KEAN	NAME MARKER Z TYPE SIZE 11 STRAIGHT / CHEVRON CUT		
	0 PLC ± - 1 PLC ± 0.2 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	PRODUCT SPEC -			
MATERIAL PVC	FINISH -	APPLICATION SPEC -	SIZE A3	CAGE CODE A00YM	DRAWING NO C-1601A0004
CUSTOMER DRAWING			WEIGHT 3.1 - 2.8g/250mm	RESTRICTED TO -	REV 12
			SCALE 10:1	SHEET 1 OF 1	