

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	12	ECN-25-356402	27OCT2025	GSK	AK

NOTES: —

1. CHARACTERS: —


- 0–9, A–Z, +, –, /,~, ≡
- 0, 1, 6 & 9 FOLLOWED BY A FULL STOP.
- HEIGHT 2.6 – 2.9 mm
- TOLERANCE (AXIAL) ±0.75
- (ROTATIONAL) ±5°

CHEVRON CUT MARKERS: —


CHARACTERS TO BE CENTRALLY DISPOSED ON MARKER FACE AND IN THE ATTITUDE SHOWN RELATIVE TO CHEVRON.

2. MARKER LENGTHS (DIMENSION 'A') : —


- WITH SINGLE MARK 3.70 – 4.50
- WITH DOUBLE MARK 6.75 – 7.25



CHEVRON CUT



STRAIGHT CUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 11FEB2020 GOPALAKRISHNA H V		 TE Connectivity			
		CHK 11FEB2020 ALAN KEAN					
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± – 1 PLC ± 0.2 2 PLC ± – 3 PLC ± – 4 PLC ± – ANGLES ± –		APVD 11FEB2020 ALAN KEAN	NAME MARKER Z TYPE SIZE 13 STRAIGHT / CHEVRON CUT –			
			PRODUCT SPEC –				
			APPLICATION SPEC –				
MATERIAL PVC			FINISH –				
			WEIGHT 4.3 – 3.9g/250mm				
			SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
			A3	A00YM	C-1601A0005	–	
CUSTOMER DRAWING					SCALE 10:1	SHEET 1 OF 1	REV 12