


NUMBER
178323

METRIC


DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT

PRINT DIST



△6	△4	178323-5
△6	△3	178323-3
△6	△2	178323-2
(FINISH)		製品番号 (PART NO.)

E	REVISED PER ECR-25-250788	F.Z	R.B	16JAN 2025
D1	REVISED PER ECO-11-005030	RK	HMR	23MAR11
LTR	REVISION RECORD	DR	CHK	DATE



推奨基板取付け穴寸法

PC 基板厚:1.6±0.1
(非累積公差)
(コネクタ搭載面)

NOTES

- MATERIAL:HOUSING:GLASS FILED THERMO
PLASTIC,POLYESTER
CONTACT:COPPER ALLOY
RETENTION LEG:COPPER ALLOY
- △2. FINISH(CONTACT AREA): 0.38μm PdNi & Au PLATING OVER NICKEL
- △3. FINISH(CONTACT AREA): 0.76μm PdNi & Au PLATING OVER NICKEL
- △4. FINISH(CONTACT AREA):2.0 μmMIN TIN
PLATED OVER NICKEL
- △5. FINISH(RETENTION LEG): TIN-LEAD PLATED
(CONTACT TAIL) OVER NICKEL
- △6. FINISH(RETENTION LEG): TIN PLATED
(CONTACT TAIL) OVER NICKEL

			 TE Connectivity		
WIRE RANGE		INSULATION DIA	NAME		
mm (AWG -)		mmφ	DOUBLE ROW (D-3100)		
MATERIAL		FINISH	DYNAMIC CONN. 6POS. VERTICAL HDR. ASS'Y		
SEE NOTE 注記参照		SEE NOTE 注記参照	一般公差 (GENERAL TOLERANCE)		
DR. 15 FEB '91 N. Matsubara		DE. 15 FEB '91 N. Matsubara	10mm以下 : ±0.3 10mm超 30mm以下 : ±0.4 30mm超 100mm以下 : ±0.5 角 度 : ±3°		
CHK. 21 MAY '91 T. Obara		APP. 21-MAY-'91 S. MANABE	SIZE	LOC	NUMBER
			A3	J	C-178323
			SCALE	REV.	SHEET
			2-1	E	1 OF 1