




REVISIONS			
P	UN	DATE	APP
S		27APR2026	JAB JC
REV PER ECH-26-300535			

WARNING - THIS DOCUMENT CONTAINS TECHNOLOGY WHOSE EXPORT IS RESTRICTED BY THE EXPORT ADMINISTRATION REGULATIONS ('EAR') PURSUANT TO 15 C.F.R. PARTS 730-774. VIOLATIONS OF THE EAR ARE SUBJECT TO SEVERE CRIMINAL PENALTIES UNDER THE EXPORT CONTROL REFORM ACT, AS AMENDED (TITLE 50, U.S.C., SEC. 480I, ET SEQ.).



1. THIS RECEPTACLE WILL MATE WITH ANY PLUG CONNECTOR WITH THE SAME INSERT ARRANGEMENT AS DEFINED BY MS18275-1.
2. MAXIMUM WIRE INSULATION USED WITH THIS RCPT. IS .072 DIA. MAX.
3. Be-Cu RETENTION CLIPS ARE INCLUDED IN INSERTS.
4. FAR SIDE REFERS TO WIDE SIDE OF KEYSTONE.
5. UL/CSA DESIGNATION STAMPED IN THIS AREA,OPTIONAL
6. THESE CONNECTORS ARE QUALIFIED TO GODDARD SPACE FLIGHT CENTER SPECIFICATION S-311-P-4.
6. CONNECTOR SUPPLIED WITH CONTACTS, AMP PART NUMBER 206793-1J (NOT INSTALLED).

OBSOLETE	.120	570513-3	206801-9
OBSOLETE	.120	LMSC 1621480-003	206801-8
OBSOLETE	.120	LMSC 1621480-003	206801-7
OBSOLETE	.120	2A014-008V-001	206801-4
OBSOLETE	.154		206801-3
	.120	311P409-3S-B-12	206801-2
	.154	311P409-3S-B-15	206801-1
REMARKS	DIA A	MARK CUSTOMER P/N	AMP P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.			
DRAWING NO		1-3-99	
REV		1-24-99	
DIMENSIONS: INCHES		NAME	
OBSOLETE PARTS:		PRODUCT SPEC	
1 PLG		APPLICATION SPEC	
2 PLG		WEIGHT	
3 PLG		CUSTOMER DRAWING	
4 PLG		SCALE	
MATERIAL		SHEET	
SEE CALLOUTS		1 of 1	
		REV S	

TE Connectivity

TE Connectivity

RECEPTACLE FOR SOCKET CONTACTS, SIZE #3, 25 POS. (NON-MAGNETIC)

RESTRICTED TO

—