





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	P	REVISED PER ECR-24-213594	01JUL2024	RK	FJS



RECOMMENDED PC BOARD LAYOUT



- ① HOUSING MATERIAL: PA66, BLACK, UL 94 V-0 RATED
- ② BRASS PER ASTM B36.
- ③ 3.81µm [.000150] MIN TIN-LEAD OVER 2.54µm [.000100] MIN COPPER OR 1.27µm [.000050] MIN NICKEL.
- ④ 0.76µm [.000030] MIN GOLD FOR A LENGTH OF 5.08 [.200] MIN FROM MATING END, 3.81µm [.000150] MIN TIN-LEAD FOR A LENGTH OF 5.36 [.211] MIN FROM OPPOSITE END, BOTH OVER 1.27µm [.000050] MIN NICKEL.
- ⑤ .000150 MIN LEAD FREE TIN OVER .000100 MIN COPPER, OR .000050 MIN NICKEL.
- ⑥ 0.76µm [.000030] MIN PRECIOUS METAL PLATE FOR A LENGTH OF 5.08 [.200] MIN FROM MATING END, 3.81µm [.000150] MIN TIN FOR A LENGTH OF 5.36 [.211] MIN FROM OPPOSITE END, BOTH OVER 1.27µm [.000050] MIN NICKEL.

	⑥	207398-7
	⑤	207398-6
OBSOLETE	④	207398-3
OBSOLETE	③	-207398-1-
FINISH		PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L.SIPE 07/07/92	TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK R.STONE 7-24-92			
		APVD A.TRAVIS 7-24-92	NAME		
		PRODUCT SPEC	PIN HDR ASSY, 10 POSN, IN-LINE, RIGHT ANGLE, SMALL METRIC CONNECTOR, METRIMATE		
MATERIAL HOUSING: CONTACTS:		APPLICATION SPEC	SIZE A2	CAGE CODE 00779	DRAWING NO C-207398
		FINISH CONTACTS: SEE TABLE	WEIGHT -	SCALE 2:1	SHEET 1 OF 1
CUSTOMER DRAWING			REV P		