







NOTES:

Housing:PBT+30%GF(UL94V-O) BLACK
Contact:Brass
" GOLD PLATING ON CONTACT AREA
100u" MATTE TIN PLATING ON SOLDER TAIL
50u" NICKEL UNDERPLATED OVERALL
HOLD DOWN:Brass,100u" TIN OVER 50u" NICKEL
Shell: Cold Roller Steel, Ni Plated
Revit:Brass,Nickel Plating

LOT NUMBER "XXXX"

- Stands For Calendar Year
- Stands For Week Number

THREADED	30 μ "Au	2311774-1
-	Contact Area	P/N
	Plating	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN AJITH PAI 09MAR2017		 TE Connectivity									
		CHK DANIEL GORENC 09MAR2017											
DIMENSIONS: mm		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME AMPLIMITE PLUG, HD22, RIGHT ANGLE, 15P — —									
		0 PLC ± — 1 PLC ± — 2 PLC ± 0.25 3 PLC ± — 4 PLC ± — ANGLES ± —											
		—											
MATERIAL —		FINISH —		SIZE A2		CAGE CODE 00779		DRAWING NO C=2311774		RESTRICTED TO —			
CUSTOMER DRAWING								SCALE 1:1		SHEET 1 of 1		REV F1	