



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D3	REVISED PER ECR-25-255998	15SEP2025	SA	DSC

- 1
- FOR 1.02 [.040] TO 2.54 [.100] WIRE INSULATION DIA
- 2
- TONGUE MATERIAL THK = 0.58±0.05 [.023±.002]
- 3
- APPLIES FROM THE METAL EDGE OF THE BARREL TO THE CENTER OF THE STUD



1 KIT = 50 PIECES	LOOSE PC	BODY & SLEEVE: COPPER (ASTM-B152) TIN PL (ASTM-B545) INSULATION: NATURAL NYLON (ASTM-D4066) TYPE 1	6-329636-0
1000	LOOSE PC		329636
QTY	PACKAGE TYPE	MATERIAL & FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA 27AUG09	 TE Connectivity				
		CHK JEFF RUTH 27AUG09					
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD TOM MICHIELUTTI 27AUG09	NAME				
	0 PLC ± -	PRODUCT SPEC	WIRE TERMINAL PIDG - RING TONGUE WIRE SIZE: 24-20 AWG				
	1 PLC ± -	—					
	2 PLC ± -	APPLICATION SPEC					
	3 PLC ± 0.20 [.008]	—					
MATERIAL SEE TABLE	4 PLC ± -	WEIGHT —	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
	ANGLES ± 0° 30'		A3	00779	C-329636	—	
CUSTOMER DRAWING			SCALE	SHEET		REV	
			10:1	1 OF 1		D3	