


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D2	REVISED PER ECR-25-260429	29OCT2025	SA	MFP

AMP WIRE RANGE	 Listed FILE E13288	 LR7189 Certified
16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED




1 WIRE INSULATION DIAMETER Ø .115 TO Ø .170

2 MATERIAL:
BODY - COPPER (QQ-C-576)
INSULATION - PVC

3 FINISH:
BODY - TIN PLATE PER ASTM B-545
INSULATION COLOR - BLUE

1000	LOOSE PIECE	34134
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 105°C [221°F]
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: 600 V MAX [1000 V FIXTURES AND SIGNS]
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 1.04-2.62mm2 [2,050-5,180]
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± 1°
MATERIAL	FINISH
2	3

DWN jr ruth 05SEP03	 TE Connectivity			
CHK T MICHIELUTTI 05SEP03				
APVD T MICHIELUTTI 05SEP03	NAME WIRE SPLICE, PARALLEL, PLASTI-GRIP, WIRE SIZE: 16-14 AWG			
PRODUCT SPEC UL 486C	SIZE A3 CAGE CODE 00779 DRAWING NO C-34134 RESTRICTED TO -			
APPLICATION SPEC 114-2161				
WEIGHT	SCALE 4:1 SHEET 1 OF 1 REV D2			
CUSTOMER DRAWING				