


REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
	G3	REVISED PER ECR-25-255998	15SEP2025	SA
				DSC

AMP WIRE RANGE	 Listed FILE E13288	 LR7189 Certified
22-16 AWG SOLID OR STRANDED	22-16 AWG SOLID OR STRANDED	22-16 AWG SOLID OR STRANDED



- 1

STAMP AMP 22-18* 1-2 APPROX AS SHOWN 22-16 TERMINALS ARE STAMPED 22-18 IN ACCORDANCE WITH MILITARY SPEC SAE AS7928 COMMERCIAL WIRE RANGE IS 22-16
- 2

WIRE INSULATION DIA: 2.67-3.56 [.105-.140]
- 3

TONGUE MATERIAL THK: 0.79^{±0.05} [.031^{±.002}]
- 4

MATERIAL: BODY - CU PER ASTM B152 SLEEVE - PVC, COLOR - RED

100	LOOSE PIECE, BOX	8-34141-1
1 KIT = 250 PIECES	LOOSE PIECE	6-34141-0
5000	ON TAPE, REEL	2-34141-1
1000	LOOSE PIECE	34141
QTY	PACKAGE TYPE	PART NO.

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 105°C [221°F]	THIS DRAWING IS A CONTROLLED DOCUMENT.	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: 600V MAX (1000V FIXTURE OR SIGN)	DIMENSIONS: mm [INCHES]	
	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 0.26-1.65mm² [509-3260] SOLID OR STRANDED	TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.20[.008] 3 PLC ± - 4 PLC ± - ANGLES FINISH ± -	
FOR ORDER ENTRY	1-800-526-5142		MATERIAL -4	
			TIN PER ASTM B545	

DWN DK SCHRUM	08/06/92	 TE Connectivity		
CHK RE HERSEY	11/10/92	NAME		
APVD M BARNABA	11/10/92	PRODUCT SPEC		
UL 486A		TERMINAL, RING TONGUE, PLASTI-GRIP, WIRE SIZE: 22-16 AWG		
APPLICATION SPEC		RESTRICTED TO		
- WEIGHT		SIZE	CAGE CODE	DRAWING NO
-		A3	00779	C-34141
CUSTOMER DRAWING		SCALE	4:1	SHEET 1 of 1
		REV	G3	