


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	T6	REVISED PER ECR-25-255998	12SEP2025	SA	DSC



AMP WIRE RANGE	RU FILE E13288	SR LR7189 Certified
6 AWG STRANDED	6 AWG STRANDED	6 AWG STRANDED

- 1 STAMP AMP 6* LOCATE APPROX AS SHOWN
- 2 TONGUE MATERIAL THK 1.14±0.08[.045±.003]
- 3 SEE TABLE FOR WIRE INSULATION DIA MAX
- 4 NOTE DELETED
- 5 TAPE ITEMS ARE ON 30.48[1.200] CENTERS
- 6 NOTE DELETED
- 7 NOTE DELETED

11.43 [.450]	3/8	9.91±0.13 [.390±.005]	1 KIT = 50 PIECES	LOOSE PC	6-52264-1
	5/16	8.33±0.13 [.328±.005]	1 KIT = 50 PIECES		6-52264-0
11.43 [.450]	3/8	9.91±0.13 [.390±.005]	500	ON TAPE	52264-5
	5/16	8.33±0.13 [.328±.005]			52264-4
11.43 [.450]	3/8	9.91±0.13 [.390±.005]	100	LOOSE PC	52264-1
	5/16	8.33±0.13 [.328±.005]			52264
WIRE INSULATION DIA	"B"	"A"	QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 105° C
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: 600 V MAX
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 10.54-16.77mm²[20,800-33,100] STANDARD
FOR ORDER ENTRY	1-800-526-5142	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.S. GOULDEN 9-29-93	STE TE Connectivity		
		CHK R. HERSEY 9-29-93			
		APVD B.BARE 9-29-93	NAME TERMINAL, RING TONGUE, PLASTI-GRIP, TM WIRE SIZE: 6 AWG		
		PRODUCT SPEC NOT AVAILABLE			
		APPLICATION SPEC 114-2161			
		WEIGHT -	SIZE A3	CAGE CODE 00779	RESTRICTED TO -
		CUSTOMER DRAWING	SCALE 4:1	SHEET 1 OF 1	REV T6