







|                |      |      |      |    |      |     |
|----------------|------|------|------|----|------|-----|
| AVAILABLE      | 51.8 | 50.6 | 54.7 | 50 | 47.4 | 160 |
| AVAILABLE      | 45.8 | 44.6 | 48.7 | 44 | 41.4 | 140 |
| NOT AVAILABLE  | 39.8 | 38.6 | 42.7 | 38 | 35.4 | 120 |
| AVAILABLE      | 33.8 | 32.6 | 36.7 | 32 | 29.4 | 100 |
| NOT AVAILABLE  | 30.8 | 29.6 | 33.7 | 29 | 26.4 | 90  |
| NOT AVAILABLE  | 27.8 | 26.6 | 30.7 | 26 | 23.4 | 80  |
| AVAILABLE      | 24.8 | 23.6 | 27.7 | 23 | 20.4 | 70  |
| AVAILABLE      | 21.8 | 20.6 | 24.7 | 20 | 17.4 | 60  |
| AVAILABLE      | 18.8 | 17.6 | 21.7 | 17 | 14.4 | 50  |
| NOT AVAILABLE  | 15.8 | 14.6 | 18.7 | 14 | 11.4 | 40  |
| NOT AVAILABLE  | 12.8 | 11.6 | 15.7 | 11 | 8.4  | 30  |
| TOOLING STATUS | E    | D    | C    | B  | A    | POS |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
單位：耗  
mm

TOLERANCES UNLESS  
OTHERWISE SPECIFIED:  
一般公差

0 PLC ± 0.3  
1 PLC ± 0.3  
2 PLC ± 0.3  
3 PLC ± 0.3  
4 PLC ANGLES ± 0.3  
FINISH 仕上

MATERIAL  
材料

DWN  
CHK  
APVD  
PRODUCT SPEC  
製品規格  
APPLICATION SPEC  
取付適用規格  
WEIGHT

NAME  
名称  
EMBOSS ASSY  
FH 0.6BTB CONNECTOR  
PLUG 4H WITH G-PLATE

SIZE  
CAGE CODE  
DRAWING NO  
番号  
A300779C-5353184

RESTRICTED TO











CUSTOMER DRAWING

SCALE  
尺度  
4:1


SHEET  
2 OF 3

REV  
D2

| REVISIONS<br>変更 |     |             |  |      |      |
|-----------------|-----|-------------|--|------|------|
| P               | LTR | DESCRIPTION |  | DATE | APVD |
|                 | -   | SEE SHEET 1 |  | -    | -    |



- ① MATERIAL : HOUSING : HIGH TEMP THERMO PLASTIC, UL94V-0  
CONTACT : COPPER ALLOY
- ② FINISH : UNDER PL Ni 0.0013mm MIN ALL OVER.  
CONTACT AREA: 0.0002mm MIN Au PL.  
SOLDERING AREA: 0.001mm MIN TIN PL.
- ③ THIS POSITION IS GROUND CIRCUIT.
- ④ THIS PRODUCT WAS COATED BY FLUX-PENETRATION  
-INHIDITING AGENT.
- ⑤ FINISH : UNDER PL Ni 0.0013mm MIN ALL OVER.  
CONTACT AREA: 0.00076mm MIN Au PL.  
SOLDERING AREA: 0.001mm MIN TIN PL.
- ⑥ OBSOLETE

|                                                                                       |                                                   |                            |                                                                                                            |           |                                                            |                 |
|---------------------------------------------------------------------------------------|---------------------------------------------------|----------------------------|------------------------------------------------------------------------------------------------------------|-----------|------------------------------------------------------------|-----------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                |                                                   | DWN                        |  TE Connectivity Ltd. |           |                                                            |                 |
|                                                                                       |                                                   | CHK                        |                                                                                                            |           |                                                            |                 |
|                                                                                       |                                                   | APVD                       |                                                                                                            |           |                                                            |                 |
| DIMENSIONS:<br>単位: 耗<br>mm                                                            | TOLERANCES UNLESS<br>OTHERWISE SPECIFIED:<br>一般公差 | PRODUCT SPEC<br>製品規格       | NAME<br>名称                                                                                                 |           | EMBOSS ASSY<br>FH 0.6BTB CONNECTOR<br>PLUG 4H WITH G-PLATE |                 |
|  | 0 PLC ± 0.3                                       | APPLICATION SPEC<br>取付適用規格 | SIZE                                                                                                       | CAGE CODE | DRAWING NO<br>番号                                           | RESTRICTED TO   |
|                                                                                       | 1 PLC ± 0.3                                       |                            | A300779                                                                                                    |           | G-5353184                                                  |                 |
| MATERIAL<br>材料                                                                        | 2 PLC ± 0.3                                       | WEIGHT                     | CUSTOMER DRAWING                                                                                           |           | SCALE<br>尺度 3:1                                            | SHEET<br>3 OF 3 |
|                                                                                       | 3 PLC ± 0.3                                       |                            |                                                                                                            |           |                                                            | REV<br>D2       |
|                                                                                       | 4 PLC ± 0.3                                       |                            |                                                                                                            |           |                                                            |                 |
|                                                                                       | ANGLES ± 3°                                       |                            |                                                                                                            |           |                                                            |                 |
|                                                                                       | FINISH<br>仕上                                      |                            |                                                                                                            |           |                                                            |                 |