




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	E1	REVISED AS PER ECR-25-235176	18SEP2025	PK	SKN

.120 DIA THRU HOLE WITH
.191 WIDE X .110 DEEP SLOT.



PANEL CUTOUT DETAIL
NTS

OBSOLETE	.040	.144	.025	.030	ONE KIT PER BAG	100	.200	.400	745245-9
OBSOLETE	.050	.136	.055	.045	BULK PACKAGED	2	.200	.400	745245-7
OBSOLETE	.040	.144	.025	.030	BULK PACKAGED	2	.265	.530	745245-6
OBSOLETE	.040	.144	.025	.030	ONE KIT PER BAG	2	.265	.530	745245-5
OBSOLETE	.040	.144	.025	.030	BULK PACKAGED	2	.200	.400	745245-3
OBSOLETE	.040	.144	.025	.030	ONE KIT PER BAG	2	.200	.400	745245-2
	F	E	D	C	PACKAGING	QUANTITY	B	A	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± -
MATERIAL ZINC	FINISH -

DWN J GALLUCCI BG 4-9-90	CHK W.LENKER 6-15-90
APVD - 7-11-90 J.WESTMAN	PRODUCT SPEC - 7-16-90 J.ASSINI
APPLICATION SPEC -	WEIGHT 0.000000
CUSTOMER DRAWING	



TE Connectivity

LATCHING BLOCK, AMPLIMITE

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-745245	-
SCALE 4:1		SHEET 1 OF 1	REV E1