


NUMBER 917542







METRIC

DEPT5670>E16625>U.DYNAMIC>U.CAD>917542.0.1.C
DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT

PRINT DIST

AMP-J
REV.10/83



推奨基板取付け寸法
PC 基板厚: 1.6 ~ 2.4 ± 0.1
(非累積公差)
(コネクタ搭載面)

RECOMENDED PC BOARD HOLE PATTERN
PC BOARD THICKNESS: 1.6 ~ 2.4 ± 0.1
(NOT ACCUMULATE TOLERANCE)
(CONNECTOR MOUNT SIDE)

NOTES

- MATERIAL: HOUSING: GLASS FILLED THERMO PLASTIC, POLYESTER (94V-0), COLOR: BLACK
TAB CONTACT: COPPER ALLOY
RETENTION LEG: BRASS
- FINISH (CONTACT AREA): 0.38μm Min. PdNi & GOLD FLASH
- FINISH (CONTACT AREA): 0.76μm Min. PdNi & GOLD FLASH
- FINISH (RETENTION LEG): TIN PLATED
(CONTACT TAIL) OVER NICKEL

Y	△4 △3	2-917542-3
	△4 △2	2-917542-2
X	△4 △3	1-917542-3
	△4 △2	1-917542-2
KEY TYPE	コンタクトのめっき (FINISH)	製品番号 (PART NO.)


G	REVISED PER ECN-26-376948	FZ	LL	19/MAR/2026
F	REVISED (FJD0-0039-03)	T.S.	SA	10/2
E	REVISED (FJD0-0120-03)	T.S.	SM	7/MAY/03
D	REVISED (FJ00-1335-97)	K.I.	I.H.	5/SEP/97
C	REVISED (FJ00-0096-97)	K.I.	Y.	3/FEB/97
B	REVISED (FJ00-5532-96)	K.I.	Y.	7/JAN/97
A	REVISED (FJ00-4619-96)	K.I.	S.M.	14/MAY/96
O	RELEASED (FJ00-1832-94)	Y.	I.S.M.	23/MAR/95
LTR	REVISION RECORD	DR	CHK	DATE

Copyright © 1995 Tyco Electronics AMP K.K. ALL RIGHTS RESERVED.	
WIRE RANGE mm (AWG -)	INSULATION DIA mm
MATERIAL SEE NOTE 注記参照	FINISH SEE NOTE 注記参照
DR. Y.Ishikawa 23/MAR/95	DE. Y.Ishikawa 23/MAR/95
CHK. S.Manabe	APP. S.Manabe

			TE Connectivity		
垂直タイプ ヘッダー アッシー					
LE ROW VERTICAL HDR ASS'Y -DYNAMIC D-5200-					
SIZE	LOC	NUMBER			
A3	J	C= 917542			
SCALE	REV.		SHEET		
1-1	G		1 of 2		


(CUSTOMER DRAWING) 顧客用図面

8,9-917542-2;AS SHOWN SEQUENTIAL TYPE



9-917542-2

(KEYING:Y)



8-917542-2

(KEYING:X)


タブコンタクト
TAB CONTACT

	回路番号			
	1	2	3	4
1 列	① Signal	① Signal	① Signal	② Ground

POINT OF SEQUENTIAL


NOTES

- MATERIAL:HOUSING:GLASS FILED THERMO PLASTIC
,POLYESTER(94V-0),COLOR:BLACK
TAB CONTACT:COPPER ALLOY
RETENTION LEG:BRASS
- FINISH (CONTACT AREA): 0.38μm Min. PdNi & GOLD FLASH
- FINISH(CONTACT AREA):0.76μmMIN GOLD PLATING
OVER Ni PLATING
- FINISH(RETENTION LEG): TIN PLATED
(CONTACT TAIL) OVER NICKEL




SECT "A"-"A"

(SCALE:2-1)



デートコード
DATE CODE

回路番号
CIRCUIT NO



リテンションレグ
RETENTION LEG

コンタクト半田付部
CONTACT TAIL

Y	④ ②	9-917542-2
X	④ ②	8-917542-2
KEY TYPE	コンタクトのめっき (FINISH)	製品番号 (PART NO.)

LTR	REVISION RECORD	DR	CHK	DATE
	SEE 1 OF 2			

Copyright © 1995 Tyco Electronics AMP K.K. ALL RIGHTS RESERVED.		NAME 4極 1列 垂直タイプ ヘッダー アッシー 4 POS SINGLE ROW VERTICAL HDR ASS'Y -DYNAMIC D-5200-	
WIRE RANGE mm²(AWG -)	INSULATION DIA mmφ	DR. Y.Ishikawa 22/MAR/'95	DE. Y.Ishikawa 22/MAR/'95
MATERIAL SEE NOTE 注記参照	FINISH SEE NOTE 注記参照	DR. Y.Ishikawa 23/MAR/'95	APP. S.Manabe 23/MAR/'95
SEE 1 OF 2		DR. Y.Ishikawa 22/MAR/'95	

TE Connectivity		SIZE A3	
LOC J		NUMBER C-917542	
SCALE 1-1		REV. G	
SHEET 2 of 2			

(CUSTOMER DRAWING) 顧客用図面

NUMBER 917542



METRIC

DEPT5670>E16625>U.DYNAMIC>U.CAD>917542.0.1.C
DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT

PRINT DIST

AMP-J
REV.10/'83