





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	NC	RELEASED PER EO P16142	17AUG1999	RDR	RDR
	A	REVISED PER EO P16286	09JUL1999	MG	MG
	C	REVISED PER PCN-25-253066	25JUN2025	UBF	CB

3D VIEW



- 5

MATERIAL: RECEPTACLE & CAP: PA66 GF15, BLACK
WEDGELOCK (INCLUDED): PBT GF30 (GREEN)
BUSBAR: COPPER ALLOY, NICKEL PLATED.
- 4


THE 4 PIN BUSBAR HAS A MAXIMUM CURRENT RATING OF 26 AMPS.
- 3

ORIENTATION OF "DEUTCH" AND "-P026" TO BE OPTIONAL.
- 2

BORDER SIGNIFIES THAT PINS 1,2,7,8 AND 3,4,5,6 ARE BUSSED TOGETHER WITH (2) 4 PIN BUSBARS.

1. THIS DT04-08PB-P026 MATES WITH DT06-08SB-XXXX (XXXX = ALL MODIFICATIONS).
CONSUKT FACTORY FOR MODIFICATIONS.

NOTES:

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.GONZALEZ		05AUG1999				TE Connectivity					
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK -		NAME DT 8 WAY REC KEY ARRANGEMENT -B- TWO 4 PIN BUSBARS-NICKEL PLATED COLOR - BLACK							
		APVD -		07SEP1999									
		PRODUCT SPEC -											
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±0.025 [0.63] 4 PLC ± ANGLES ±		APPLICATION SPEC -		SIZE A2		CAGE CODE 00779		DRAWING NO C=DT04-08PB-P026		RESTRICTED TO -	
		FINISH -		WEIGHT -									
		finish_spec_2		CUSTOMER DRAWING									
						SCALE 3.000		SHEET 1		OF 1		REV C	