


D

printed on 4 Nov 2024 13:46 (Eastern Standard Time) from TE354946





A

© 2024 TE Connectivity. All Rights Reserved.



2X DRILL AND TAP
BLIND HOLE FOR
1/4-20 FASTENER

**RECOMMENDED MOUNTING
DETAIL**



4. FLANGE SEAL IS INTENDED FOR NON-PRESSURIZED FLUID SPLASH ONLY,
P/N: 1013-003-1206 SUPPLIED SEPARATELY.

3. MATERIAL:
SHELL: PA66 GF15 (BLACK)
WELD CAP: PA66 GF15 (BLACK)
GROMMET: VMQ (RED-ORANGE)
INSERTS: STAINLESS STEEL

2. THIS RECEPTACLE MATES WITH THE DT06-12SA-XXXX PLUG.
(XXXX ALL MODIFICATIONS). CONSULT FACTORY FOR MODIFICATIONS.

1. FOR CONTACTS AND WIRE PERFORMANCE AND APPLICATION CHARACTERISTICS
SEE ENVELOPE DRAWING 0425-015-0000 AND 0425-017-0000.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED PER E.O. P19337	03AUG06	-	RDR
	C	REVISED PER E.O. P20545	30SEP10	-	SB
	CI	REVISED PER PCN-24-225053	07OCT2024	RK	CB

CONTACT SIZE	MIN. INSUL. O.D.	MAX. INSUL. O.D.	WIRE RANGE [mm ²] REF ONLY
16	.088 [2.24]	.145 [3.68]	14-20 AWG [2.5-0.5]

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES[mm]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±.025[.064] 4 PLC ± ANGLES ±
MATERIAL	FINISH
-	-
-	-

DWN	T. YOHANNES	22JULY04
CHK	B. BYFORD	04AUG10
APVD	S. BEARD	02AUG10
PRODUCT SPEC	108-151009	
APPLICATION SPEC	114-151009	
WEIGHT	52.52 g	
CUSTOMER DRAWING;		

NAME 12 WAY RECEPTACLE-LE17 MOD. COLOR: BLACK DT SERIES			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	DT04-12PA-LE17	-
SCALE		SHEET	OF
1:1		1	1
REV		CI	