






3D VIEW



5. MATERIAL: RECEPTACLE & CAP: PA66 GF15, BLACK WEDGELOCK (INCLUDED): PBT GF30, GREEN BUSBAR: COPPER ALLOY, NICKEL PLATED.
4. THE MAXIMUM CURRENT RATING FOR THE 6 PIN BUSBAR IS 39 AMPS.
3. BORDER SIGNIFIES THAT PINS 1,2,3,10,11,12 AND PINS 4,5,6,7,8,9 ARE BUSSED TOGETHER WITH 6 PIN BUSBARS.
2. ORIENTATION OF "DEUTSCH" AND "-P026" TO BE OPTIONAL.

1. THIS DT04-12PB-P026 MATES WITH DT06-12SB-XXXX (XXXX = ALL MODIFICATIONS). CONSULT FACTORY FOR MODIFICATIONS.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. GONZALEZ	08MAY1999	 TE Connectivity		
		CHK -	-			
DIMENSIONS: INCHES[MM]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S. BREWD	05JUL2012	NAME DT 12 WAY REC KEY ARRANGEMENT -B- 6 PIN BUSBAR-PLATED COLOR BLACK
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±0.025[0.63] 4 PLC ± ANGLES ± FINISH -		PRODUCT SPEC 108-151009		
				APPLICATION SPEC 114-151009		
MATERIAL 5				WEIGHT 26g	SIZE A3	CAGE CODE 00779
				CUSTOMER DRAWING	SCALE 2:1	DRAWING NO C-DT04-12PB-P026
					SHEET 1	OF 1
					REV B1	RESTRICTED TO -