


REVISIONS			
LT#	DESCRIPTION	DATE	APPROVED
N/C	INITIAL RELEASE, ECN NO. T-4125	8-9-82	93



NOTES:

- MATERIAL; I-A SOCKET WAFER; INSERT MATERIAL HIGH GRADE POLYARYLENE THERMOPLASTIC
I-B SOCKET CONTACT; COPPER ALLOY PER QQ-B-750
- FINISH; 2-A SOCKET WAFER; FINISH TO BE MOLDED
2-B SOCKET CONTACT ENGAGING AREA; GOLD PLATE PER MIL-G-45204, CLASS I
2-C CONTACT TAIL; SOLDER COATED PER QQ-S-571 Sn63
- WAFER; WAFER DESIGNED FOR USE WITH CONNECTORS DESIGNED TO **Raychem** SPECIFICATION D-6012
- SOCKET ONE; SOCKET NUMBER ONE MARKED IN CONTRASTING COLOR.
- WEIGHT (MAX);

LBS.	GRAMS
.0044	2.02

©Raychem Corporation 1982

SPECIFICATION CONTROL DRAWING

ITEM	QTY	PART NO	DWG OR SPEC. NO	DESCRIPTION
PARTS LIST				
THIRD ANGLE PROJECTION		MATERIAL	DRAWN <i>Hawkins</i>	DATE
FINISH		DEC. XXX	CHECKED <i>B</i>	DATE
NEXT ASSY		USED ON	APPROVED <i>B</i>	DATE 8-9-82
APPROVED <i>B</i>		DATE 4-22-83	Raychem RAYCHEM CORPORATION 300 CONSTITUTION DRIVE MENLO PARK, CALIFORNIA 94025	
THIS DRAWING AND THE INFORMATION SET FORTH HEREON ARE THE PROPERTY OF RAYCHEM CORPORATION AND ARE TO BE HELD IN TRUST AND CONFIDENCE. PUBLICATION, DUPLICATION, DISCLOSURE, OR USE FOR ANY PURPOSE NOT EXPRESSLY AUTHORIZED IN WRITING BY RAYCHEM CORPORATION IS PROHIBITED.				
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES AND TOLERANCES ARE		DEC. XXX	ANGLES	MM
.02		.005		
PROJECT NO		TITLE WAFER "B1" SOCKET, SPECIAL 1" FOR USE IN MTC100 2" CONNECTOR, 125°C OPERATING TEMP. FOR 20-26 AWG ROUND WIRE TERMINATION MTC100 SERIES		
B		FSCM NO	DWG NO	
06090		MTC100-YBI-005		
SCALE NONE		DO NOT SCALE THIS DWG SHEET OF		

If this document is printed it becomes uncontrolled.
Check with the web for latest revision.