



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A2	ECR-16-016026	14NOV2016	N . P	X . X
	A3	ECR-19-006141	02JUL2020	G . W	C . W
	B	ECR-22-132011	12JUL2022	B . P	C . W
	B1	ECR-25-236292	16APR2025	G . W	C . W



NOTE:

1. MATERIAL:
 - ITEM NO.1:NUT -ZINC DIE-CAST,NICKEL PLATED
 - ITEM NO.2:HOUSING -PA
 - ITEM NO.3:CONTACT -BRONZE
 - ITEM NO.4: HOUSING BODY: -BRASS
2. CONTACT FINISH:
 - GOLD OVER NICKEL OR SILVER OVER NICKEL
3. CABLE WIRES:
 - FOR 2~5 PIN:
 - 24AWG/0.25mm²...18AWG/0.75mm² (WITHOUT FERRULE)
 - 26AWG/0.14mm²...20AWG/0.50mm² (WITH FERRULE)
 - FOR 8 PIN:
 - 24AWG/0.25mm²...20AWG/0.50mm² (WITHOUT FERRULE)
 - 26AWG/0.14mm²...22AWG/0.34mm² (WITH FERRULE)
4. ALLDIMENSIONS ARE FOR NOMINAL REFERENCE ONLY UNLESS OTHERWISE STATED
5. PACKAGEING: IPIECE IN A BAG
6. PN INFORMATION

T411201XXXX-000

CONTACT FINISH:
1: GOLD OVER NICKEL
2: SILVER OVER NICKEL

NUMBERS OF PINS:
02: 2 PINS
03: 3 PINS
04: 4 PINS
05: 5 PINS
08: 8 PINS

CABLE OUTLET:
1: PG7(CABLE FEED: 4-6mm)
2: PG9(CABLE FEED: 6-8mm)

T4112012081-001	RPC-M12-FR-8CON-PG9-SHU-LN
T4112012051-001	RPC-M12-FR-5CON-PG9-SHU-LN
T4112012081-000	RPC-M12-FR-8CON-PG9-SHU
T4112011081-000	RPC-M12-FR-8CON-PG7-SHU
T4112012082-000	RPC-M12-FR-8CON-PG9-SH
T4112011082-000	RPC-M12-FR-8CON-PG7-SH
T4112012051-000	RPC-M12-FR-5CON-PG9-SHU
T4112011051-000	RPC-M12-FR-5CON-PG7-SHU
T4112012052-000	RPC-M12-FR-5CON-PG9-SH
T4112011052-000	RPC-M12-FR-5CON-PG7-SH
T4112012041-000	RPC-M12-FR-4CON-PG9-SHU
T4112011041-000	RPC-M12-FR-4CON-PG7-SHU
T4112012042-000	RPC-M12-FR-4CON-PG9-SH
T4112011042-000	RPC-M12-FR-4CON-PG7-SH
T4112012031-000	RPC-M12-FR-3CON-PG9-SHU
T4112011031-000	RPC-M12-FR-3CON-PG7-SHU
T4112012032-000	RPC-M12-FR-3CON-PG9-SH
T4112011032-000	RPC-M12-FR-3CON-PG7-SH
T4112012021-000	RPC-M12-FR-2CON-PG9-SHU
T4112011021-000	RPC-M12-FR-2CON-PG7-SHU
T4112012022-000	RPC-M12-FR-2CON-PG9-SH
T4112011022-000	RPC-M12-FR-2CON-PG7-SH
TE PN	TYPE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 24AUG2015 Nick Pan CHK 24AUG2015 Kobby Zhao APVD 24AUG2015 Xiang Xu		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.25 2 PLC ±0.15 3 PLC ± 4 PLC ± ANGLES ± FINISH		NAME M12 FEMALE, A CODE, RA SHIELDED CONNECTOR SCREW TERNIMAL	
		PRODUCT SPEC 108-106140 APPLICATION SPEC 114-137144		SIZE A2	
MATERIAL - -		WEIGHT - CUSTOMER DRAWING		CAGE CODE - DRAWING NO C-T411201XXXX000	
				RESTRICTED TO REV B1	
				SCALE 2:1 SHEET 1 OF 1	