






REV. 0
DCO 143953

COIL: @ 25°C
RESISTANCE 880 OHMS ±10%
NOMINAL VOLTAGE 18.0 VDC
MUST OPERATE 10.5 VDC
MUST RELEASE 6.0 VDC MAX., 0.91 VDC MIN.

ENVIRONMENT:
VIBRATION 10 Hz TO 3000 Hz @ 30 g's
SHOCK 75 g's 6 MS. DURATION
TEMPERATURE -65 °C TO +125 °C
NOTES: OPERATE TIME 2.0 MS MAX.
RELEASE TIME 1.5 MS MAX.
CONTACT STABILIZATION 2.0 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. B.D. 25OCT2004 CK. JERRY C. 10/25/04

CII Technologies
advanced control electronic solutions

CUST. QPL
CUST. NO. M39016/9-023P REV.

"JMA" RELAY

JMAP-18XP