






P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—




5,8,9-1123309-2;AS SHOWN
SEQUENTIAL TYPE



	回路番号	
	1	2
B 列	① Signal	② Ground
A 列	③ Signal	③ Signal

POINT OF SEQUENTIAL



1. MATERIAL:HOUSING:GLASS FILED THERMO PLASTIC
,POLYESTER(94V-0),COLOR:BLACK
TAB CONTACT:COPPER ALLOY
RETENTION LEG:BRASS

- △2. FINISH(CONTACT AREA):0.38μmMIN GOLD PLATING
OVER Ni PLATING
- △3. FINISH(CONTACT AREA):0.76μmMIN GOLD PLATING
OVER Ni PLATING
- △4. FINISH(RETENTION LEG): TIN PLATED
(CONTACT TAIL) OVER NICKEL
- △5. OBSOLETE PARTS : OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

KEY TYPE	CONTACT FINISH	PART NO.	STATUS
XY	△4 △2	5-1123309-2	△5 OBSOLETE
YY	△4 △2	9-1123309-2	
XX	△4 △2	8-1123309-2	OBSOLETE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K.IKEDA 07NOV1997	TE Connectivity Ltd.		
DIMENSIONS: mm		CHK N.MATSUBARA 26NOV1997			
		APVD S.MANABE 10DEC1997	NAME DOUBLE ROW HEADER ASSY 4P H-TYPE DYNAMIC D-5200 D		
		PRODUCT SPEC 108-5453			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC 114-5246			
MATERIAL SEE NOTE		WEIGHT	SIZE A3	CAGE CODE 00779	DRAWING NO C-1123309
		FINISH	RESTRICTED TO —		
		SEE NOTE	SCALE 1:1		
			SHEET 2 OF 2		
			REV F		
			CUSTOMER DRAWING		