


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B3	REV PER ECR-22-149214	18AUG2022	LP	DSC

AMP
WIRE RANGE

2/0 AWG
SOLID OR STRANDED



- 1
- STAMP "AMP 2/OW* ", LOCATED APPROX AS SHOWN

2

3

4

5

6

25	LOOSE PIECE	132104-2
QTY	PACKAGE TYPE	PART NO.

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 343°C [650°F]
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: N/A
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 60.6-76.3mm²[119,500-150,000] SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 25JAN10	TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK T MICHELUTTI 25JAN10			
		APVD T MICHELUTTI 25JAN10	NAME TERMINAL, RING TONGUE, STRATO-THERM, HR, SOLISTRAND, WIRE SIZE: 2/0 AWG		
		PRODUCT SPEC -	APPLICATION SPEC 114-2162		
MATERIAL		WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C-132104
4		5	CUSTOMER DRAWING		
			SCALE 2:1	SHEET 1 OF 1	REV B3