


LOC	DIST	REVISIONS						
		P	LTR	DESCRIPTION	DATE	DWN	APVD	
J	-							
			A	REVISED	08JUL2024	M.J	T.S	

-1: 本図
-1: AS SHOWN



注記

1. 全面に1 μ mMINの銅下地メッキの上に
3 μ mMINのニッケルメッキ

② 緩み止め剤を塗布

NOTES

1. FINISH: NICKEL PL. 3 μ mMIN THK.
OVER Cu UNDER PL. 1 μ mMIN THK.

② TO APPLY THREAD LOCK ADHESIVE

RELEASED FOR PUBLICATION

THIS DRAWING IS UNPUBLISHED.

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

© COPYRIGHT 19

DIMENSIONS: 単位 概 mm		DWN M.HIGO 3/FEB/'00	WIRE RANGE 適合電線断面積 -		INSULATION DIA 被覆外径 -			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK 7/FEB/'00	MATERIAL 炭素鋼材 CARBON STEEL		FINISH 仕上 ニッケルメッキ NICKEL PLATING			
一般公差 10 μ : ± 0.2 30 μ : ± 0.25 100 μ : ± 0.3 ANGLE : $\pm 3^\circ$		APVD M.HIGO	TE TE Connectivity					
PRODUCT SPEC 製品規格 -			NAME 名称 固定ねじ ダイナミック D-2000 50P ドロフタイプ用 FIXED HEAD SCREW FOR DYNAMIC D-2000 50P DRAWER TYPE					
APPLICATION SPEC 取付適用規格 -			SIZE A4	CAGE CODE 00779	DRAWING NO C- 1376059	RESTRICTED TO -		
WEIGHT 1.15g			SCALE 尺度 4-1					
CUSTOMER DRAWING			SHEET 1		OF 1	REV A		