







REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN APVD
	R	REVISED PER ECR-23-165705	18AUG2023	WH LC
	S	REVISED PER ECR-25-265809	19DEC2025	NH JH

- 1 MATERIAL : NYLON, UL94V-0, COLOR: NATURAL ;
2. APPLICABLE CONTACT P/N: 1123721-2 ;
3. MATING CONN. P/N: □ -1744037- □ ;
- 4 P/N WITH TPA STRUCTURE ;



26.90	29.30	6	2-1744036-6
57.38	59.78	12	1-1744036-2
52.28	54.70	11	1-1744036-1
47.22	49.62	10	1-1744036-0
42.14	44.54	9	1744036-9
37.06	39.46	8	1744036-8
31.98	34.38	7	1744036-7
26.90	29.30	6	1744036-6
21.82	24.22	5	1744036-5
16.74	19.14	4	1744036-4
11.66	14.06	3	1744036-3
6.58	8.98	2	1744036-2
DIM B	DIM A	CKT	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER CHK D. BOSSI APVD D. BOSSI	07OCT2004 07OCT2004 07OCT2004	NAME	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	
mm		0 PLC ±0.25 1 PLC ±0.25 2 PLC ±0.13 3 PLC ± 4 PLC ±		APPLICATION SPEC	
MATERIAL		WEIGHT		RESTRICTED TO	
-		-		-	
-		CUSTOMER DRAWING		SCALE N/A	
				SHEET 1 OF 1	
				REV S	