






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A		RELEASED PER ECO-20-008335	15JUN2020	BKW	SW
B		RELEASED PER ECN-22-190035	14DEC2022	CX	DZ
C		REVISED PER ECR-23-169880	21MAR2023	MV	DZ
CI		REVISED PER ECR-25-244123	16MAY2025	C.X	J.H

- 1 MATERIAL: PA, GLASS FILLED, COLOR: SEE TABLE
- 2 MATERIAL MARK: PA GF
- 3 KEYING ID MARK
4. COUNTERPART: DIFFERENT ROWS OF TERMINAL AND TPA CANNOT BE USED INTERCHANGEABLY. HEADER: PLEASE SEE TABLE

PLUG HOUSING	COUNTERPART		
	OPTIONS	TERMINAL	TPA
-2350224-	OPTION 1	2350223-1	*-2357686-*
-2350224-	OPTION 2	2486278-1/2	*-2487783-*



5-2336678-0	5-2232829-0	5-2232826-0	22.25	20.55	6.90	BLACK	KEY B	1*10	3-2350224-0
4-2336678-9	4-2232829-9	4-2232826-9	20.25	18.55	6.90	BLACK	KEY B	1*9	2-2350224-9
4-2336678-8	4-2232829-8	4-2232826-8	18.25	16.55	6.90	BLACK	KEY B	1*8	2-2350224-8
4-2336678-7	4-2232829-7	4-2232826-7	16.25	14.55	6.90	BLACK	KEY B	1*7	2-2350224-7
4-2336678-6	4-2232829-6	4-2232826-6	14.25	12.55	6.90	BLACK	KEY B	1*6	2-2350224-6
4-2336678-5	4-2232829-5	4-2232826-5	12.25	10.55	6.90	BLACK	KEY B	1*5	2-2350224-5
4-2336678-4	4-2232829-4	4-2232826-4	10.25	8.55	6.90	BLACK	KEY B	1*4	2-2350224-4
4-2336678-3	4-2232829-3	4-2232826-3	8.25	6.55	7.30	BLACK	KEY B	1*3	2-2350224-3
4-2336678-2	4-2232829-2	4-2232826-2	6.25	4.55	5.30	BLACK	KEY B	1*2	2-2350224-2
2-2336678-0	2-2232829-0	2-2232826-0	22.25	20.55	6.90	NATURAL	KEY A	1*10	2-2350224-0
1-2336678-9	1-2232829-9	1-2232826-9	20.25	18.55	6.90	NATURAL	KEY A	1*9	1-2350224-9
1-2336678-8	1-2232829-8	1-2232826-8	18.25	16.55	6.90	NATURAL	KEY A	1*8	1-2350224-8
1-2336678-7	1-2232829-7	1-2232826-7	16.25	14.55	6.90	NATURAL	KEY A	1*7	1-2350224-7
1-2336678-6	1-2232829-6	1-2232826-6	14.25	12.55	6.90	NATURAL	KEY A	1*6	1-2350224-6
1-2336678-5	1-2232829-5	1-2232826-5	12.25	10.55	6.90	NATURAL	KEY A	1*5	1-2350224-5
1-2336678-4	1-2232829-4	1-2232826-4	10.25	8.55	6.90	NATURAL	KEY A	1*4	1-2350224-4
1-2336678-3	1-2232829-3	1-2232826-3	8.25	6.55	7.30	NATURAL	KEY A	1*3	1-2350224-3
1-2336678-2	1-2232829-2	1-2232826-2	6.25	4.55	5.30	NATURAL	KEY A	1*2	1-2350224-2
RIGHT ANGLE SMT	VERTICAL SMT	VERTICAL TH	DIM "C"	DIM "B"	DIM "A"	COLOR	KEYING	POSITIONS	PART NUMBER
COUNTER PART									

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC
ANGLES
FINISH

±
±
±
±
±
±
±

MATERIAL

1

DWN
B. WEAVER
CHK
C. YI
APVD
T. BENCHOFF

21JUN2019
21JUN2019
21JUN2019

PRODUCT SPEC
108-143160
APPLICATION SPEC
114-143160
WEIGHT
-

NAME
PLUG HOUSING, SG1 2.0
-
-

SIZE
A

CAGE CODE
00779

DRAWING NO
2350224

RESTRICTED TO
-

CUSTOMER DRAWING





SCALE
12:1


SHEET
1

OF
3

REV
C


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. WEAVER	21JUN2019		 TE Connectivity	
		CHK C. YI	21JUN2019			
DIMENSIONS:		APVD T. BENCHOFF	21JUN2019		NAME PLUG HOUSING, SGI 2.0	
mm		PRODUCT SPEC				
		108-143160			SIZE A	
		APPLICATION SPEC				
		114-143160				
		WEIGHT				
MATERIAL		CUSTOMER DRAWING			SCALE 12:1	
					SHEET 2 OF 3	
					REV C	

KEYING A SHOWN


2 POSITION




3 POSITION




4 POSITION




5 POSITION




6 POSITION




7 POSITION



8 POSITION



9 POSITION



10 POSITION

