






P	LTR	DESCRIPTION	DATE	DWN	APVD
	NC	NEW RELEASE PER E.O.P18931	06MAR2025	-	ROR
	B	REVISED PER PCN-24-226269	03JAN2025	AJT	MB

3D VIEW



4. MATERIAL: CONNECTOR: PA66 GF15, GRAY
CAP:PA66 GF15, BLACK
WEDGE LOCK (INCLUDED): PBT GF30 (GREEN)
PINS: COPPER ALLOY, NICKEL PLATED

3. THE 4 PIN BUSBAR HAS A MAXIMUM CURRENT RATING OF 26 AMPS.

2. ORIENTATION OF "DEUTSCH" AND "-P021" TO BE OPTIONAL.

1. MATES WITH DT06-4S-XXXX (XXXX = ALL MODIFICATIONS).
CONSULT FACTORY FOR MODIFICATIONS.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.YOHANNES 19MAY2005	 TE Connectivity		
		CHK B.BYFORD 15APR2009			
DIMENSIONS: INCHES[mm]		APVD -	NAME DT 4 WAY RECEPTACLE PIN BUSBAR NICKEL PLACED COLOR: GRAY		
		PRODUCT SPEC 108-151009			
		APPLICATION SPEC 114-151009			
		WEIGHT 11.34 g	SIZE A3	CAGE CODE 00779	DRAWING NO C-DT04-4P-P021
MATERIAL 4		FINISH -	RESTRICTED TO -		
CUSTOMER DRAWING			SCALE 5:2	SHEET 1 OF 1	REV B