

THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION	
© COPYRIGHT 20		ALL RIGHTS RESERVED.	
ITEM	DESCRIPTION	MATERIAL	OTHERS
1	FEMALE CONTACT	BRONZE	GOLD PLATED
2	HOUSING	NYLON	BLACK
3	COUPLING NUT	ZAMACK	NICKEL PLATED
4	OVER-MOLDING	POLYURETHANE	BLUE
5	CABLE	-	-
6	LABEL	-	-



REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN
		SEE SHEET 1		

D



C

B

A



TECHNICAL DATA	T41513X0005-B01
RATED VOLTAGE	60V
RATED IMPULSE VOLTAGE	1500V
RATED CURRENT	4A
POLLUTION DEGREE	3
OVERVOLTAGE CATEGORY	II
MATERIAL GROUP	II
DEGREE OF PROTECTION	IP67



WIRES: 0.34mm ² (22AWG) WIRE COLOR: WH/BR/BK/BL/GR OD: 5.8MM FOR 5P	254±6mm	M12带PUR线A型直型5针母插 0.254M(TE)	RPC-M12-FS-5CON-PUR-0.254	5	T4151320005-B01
WIRES: 0.34mm ² (22AWG) WIRE COLOR: WH/BR/BK/BL/GR OD: 5.2MM FOR 5P	254±6mm	M12带PVC线A型直型5针母插 0.254M(TE)	RPC-M12-FS-5CON-PVC-0.254	5	T4151310005-B01
CABLE CHARACTERISTIC 线缆特性	LENGTH "L" 长度 "L"	DESCRIPTION 描述	TYPE 型号	POS. 针数	TABLE 2 TE PN
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN HAO WANG CHK KOBBY ZHAO APVD XIANG XU	TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC 108-106140	NAME M12X1 STRAIGHT RECEPTACLE, FREE END A-CODE, UNSHIELDED,	
MATERIAL		FINISH	APPLICATION SPEC 114-137144	SIZE A2	CAGE CODE -
			WEIGHT -	DRAWING NO C-T41513X00XX00X	RESTRICTED TO
CUSTOMER DRAWING			SCALE 1:1	SHEET 2 OF 2	REV B4

D

C

B

A