


PART NUMBER	FIRST USED	AWB	INS RANGE		COLOR CODE
			MAX.	MIN.	
69411	69525-1	24	.065	.046	RED
69411-4	69526-2	22	.065	.046	ORANGE
69411-7	69525-1	22	.065	.046	ORANGE
1-69411-0	69525-1	24	.065	.046	RED
1-69411-1	69526-2	26	.065	.046	BROWN
1-69411-2	69525-1	24	.065	.046	RED
1-69411-3	69526-2	24	.065	.046	RED
1-69411-4	69525-1	22	.065	.046	ORANGE
1-69411-5	69525-1	24	.065	.046	RED
1-69411-6	69526-2	22	.065	.046	ORANGE
1-69411-8	69525-1	24	.065	.046	RED
1-69411-9	69526-2	26	.065	.046	BROWN



C	REVISED	B.S.		10-27 75
B	REVISED	FN		12-20 75
A	REVISED	PL		5-9- 68
LTR	REVISION RECORD	DR	CHK	DATE

										DWG SIZE		UNPUBLISHED COPY MUST BE REPRODUCED AND PUBLISHED BY AMP INCORPORATED ©1968 AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.										REMARKS										ITEM NO																			
REQUIRED PER ASSEMBLY										CUSTOMER COPY REFERENCE ONLY																																									
										DR B. Shenfeld 4-5-68										MATERIAL AND COATING STEEL										 AMP INCORPORATED HARRISBURG, PENNA.																					
										CHK E. J. Link 4-9-68										ELECTROLESS NICKEL										CLASS + + +																					
										DE										WIRE - RANGE - INSULATION SEE TABLE SEE TABLE										TYPE TERMI-POINT																					
										RSL E. J. Link 4-9-68										TOLERANCE EXCEPT AS NOTED ± .015 ± 1° 0'										SCALE H										LOC M										NO B 69411	
DESCRIPTION										NAME MANDREL																																									