

Thermofit[®] Molded Parts
Specification Control Drawing
Limited Distribution

Part Number : 202D1XX-XX-07
Description : Boot, Straight, With Lips

NOTES

1. All dimensions are in $\frac{\text{inches}}{\text{[millimeters]}}$
2. Dimensions appearing in table are as follows:
a - As Supplied
b - After Unrestricted Recovery
3. Coating is optional. As supplied dimensions appearing in table are for uncoated parts. When coating is added, entry diameters will be reduced by .06 max.
4. Part numbers 202D163-X-07 thru 202D196-X-07 will have two lips.




TABLE OF DIMENSIONS											
PART NUMBER	H		J			P	R	S	T	JO	W
	Min a	Max b	Min -3-4 -25 a	Min -12 c	Max b	±10% b	Ref b	Ref b	Ref b	±10% b	±20% b
202D121-XX-07	.92 [23,3]	.41 [10,5]	.92 [23,3]	.49 [12,4]	.22 [5,6]	1.03 [26,1]	.36 [9,1]	.12 [3,1]	.04 [1,0]	.40 [10,2]	.07 [1,8]
202D132-XX-07	1.12 [28,4]	.56 [14,2]	1.12 [28,4]	.58 [14,7]	.26 [6,6]	1.69 [42,9]	.62 [15,7]	.12 [3,1]	.04 [1,0]	.65 [16,6]	.07 [1,8]
202D142-XX-07	1.22 [31,0]	.70 [17,8]	1.22 [31,0]	.63 [16,0]	.28 [7,2]	1.83 [46,5]	.59 [15,0]	.12 [3,1]	.04 [1,0]	.70 [17,8]	.08 [2,0]
202D153-XX-07	1.42 [36,1]	.88 [22,3]	1.42 [36,1]	.73 [18,5]	.33 [8,4]	2.35 [59,7]	.83 [21,1]	.12 [3,0]	.04 [1,0]	.82 [20,8]	.08 [2,0]
202D163-XX-07	1.68 [42,7]	1.11 [28,2]	1.68 [42,7]	.87 [22,0]	.39 [9,9]	3.28 [83,3]	1.42 [36,0]	.12 [3,1]	.065 [1,65]	.97 [24,6]	.09 [2,3]
202D174-XX-07	2.04 [51,8]	1.38 [35,1]	2.04 [51,8]	1.39 [35,3]	.62 [15,8]	4.33 [109,9]	1.74 [44,2]	.12 [3,1]	.065 [1,65]	1.56 [39,6]	.13 [3,3]
202D185-XX-07	2.60 [66,0]	1.75 [44,5]	2.60 [66,0]	1.80 [45,7]	.80 [20,4]	5.70 [144,7]	2.51 [63,7]	.12 [3,1]	.08 [2,0]	1.90 [48,3]	.16 [4,06]
202D196-XX-07	3.22 [81,7]	2.27 [57,6]	3.22 [81,7]	2.25 [57,1]	1.00 [25,4]	5.53 [140,4]	2.28 [57,9]	.12 [3,0]	.08 [2,0]	1.88 [47,8]	.16 [4,06]

Raychem
RAYCHEM CORPORATION
300 CONSTITUTION DRIVE
MENLO PARK, CALIFORNIA 94025

Revision : G
Date : 2/12/97
Part Number : 202D1XX-XX-07
Description : Boot, Straight, With Lips

Thermofit[®] Molded Parts
Specification Control Drawing
Limited Distribution

Part Number : 202D1XX-XX-07
Description : Boot, Straight, With Lips

COMPATABILITY CHART					
MATERIAL DASH NO.	MATERIAL DESCRIPTION	RT SPEC	COATING SLASH NO.	COATING S NO.	COATING DESCRIPTION
-3	Polyolefin, Semi-rigid	RT-301	/42,/86	S-1017,S-1048	Adhesive
-4	Polyolefin, Flexible	RT-1304	/42,/86	S-1017,S-1048	Adhesive
-12	*VITON, Flexible	RT-1312	N/A		
-25	Elastomer, Fluid Resistant	RT-1325	N/A		

*VITON is a Registered Trademark of Dupont

ORDERING INFORMATION

202D1XX -XX -07 /XX

Base port number _____

Material dash number _____
(See Compatability Chart)

Modification number _____
(If necessary, see front of scd binder for a complete list)

Adhesive slash number _____
(If necessary, see Compatability Chart)

If this document is printed it becomes uncontrolled.
Check for the latest revision.

THIS DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE; CONSULT YOUR
NEAREST FIELD REPRESENTATIVE FOR CURRENT REVISION

Raychem
RAYCHEM CORPORATION
300 CONSTITUTION DRIVE
MENLO PARK, CALIFORNIA 94025

Revision : G
Date : 2/12/97
Part Number : 202D1XX-XX-07
Description : Boot, Straight, With Lips