





P	LTR	DESCRIPTION	DATE	DWN	APVD
	CI	PART STATUS CHANGE TO DISCONTINUNACE	19JUN2026	NS	PS




1986774-4 IS OBSOLETE

1. MATERIAL:
HOUSING - PA, UL94 V0, COLOR - GREEN
PUSH BUTTON - PA (POLYAMIDE), COLOUR - ORANGE
CLAMPING SPRING - STAINLESS STEEL
PIN - COPPER ALLOY(CuCr) -BRIGHT TIN PLATED,
OVERNICKEL UNDERPLATE
2. MECHANICAL:
MIN. PC BOARD HOLES DIAMETER : 1.2 mm
MAX. PC BOARD THICKNESS : 2.4 mm
WIRE STRIPPING LENGTH : 11 mm
3. ELECTRICAL:
WIRE RANGE : 12-30 AWG (2.5mm2 TO 0.2mm2)
RATED VOLTAGE : 300V
RATED CURRENT : 15A
CONTACT RESISTANCE : <15 m Ohm
INSULATION RESISTANCE : >1000 M Ohm (500V DC)
4. OPERATING TEMPERATURE RANGE : -40°C TO +105°C



	61.50	12	1-1986774-2
	56.50	11	1-1986774-1
	51.50	10	1-1986774-0
OBSOLETE	46.50	9	1986774-9
OBSOLETE	41.50	8	1986774-8
	36.50	7	1986774-7
OBSOLETE	31.50	6	1986774-6
OBSOLETE	26.50	5	1986774-5
OBSOLETE	21.50	4	1986774-4
OBSOLETE	16.50	3	1986774-3
	11.50	2	1986774-2
	"L"	POLE	PART NO



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.5

1 PLC ±0.25

2 PLC ±0.25

3 PLC ±0.25

4 PLC ±0.25

ANGLES ±1°

FINISH -

DWN 11OCT2012
KIRAN HOLAL

CHK 11OCT2012
MARK BRUBAKER

APVD 11OCT2012
MARK BRUBAKER

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME
SPRING TYPE, SIDE WIRE ENTRY
TERMINAL BLOCK PITCH 5.00MM

SIZE
A300779

CAGE CODE
C-1986774

DRAWING NO

RESTRICTED TO
-

SCALE 3:1 SHEET 1 OF 1 REV CI