






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	P	REVISED PER ECR-26-286663	29JUL2026	GSK	CAS



DETAIL A




DETAIL B

1. CAVITY IDENTIFICATION ON FRONT AND REAR FACE.
2. WILL ACCEPT SEVEN (7) TYPE XII SOCKET CONTACTS.
- 3 #4 FASTENER RECOMMENDED FOR MOUNTING.
- 4 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 5 TE LOGO AND PART NUMBER LOCATED ON ANY FLANGE EDGE

4 OBSOLETE

4-40 THREADED INSERTS	NO	A	206227-6
3.81±0.08 [.150±.003]	YES	A	206227-5
3.81±0.08 [.150±.003]	NO	B	206227-2
3.81±0.08 [.150±.003]	NO	A	206227-1

C		PERIPHERAL SEAL	SEE DETAIL	PART NUMBER						
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. HARDY 05/31/94	 TE Connectivity							
DIMENSIONS: mm [INCHES]		CHK W.G. LENKER 06/08/94								
		APVD A. FRANTUM 07/13/94	NAME							
		PRODUCT SPEC	RECEPTACLE HOUSING, REVERSE							
		108-10024	SEX, SHELL SIZE 23, CPC							
		APPLICATION SPEC								
MATERIAL THERMOPLASTIC, BLACK		WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO				
FINISH			A1	00779	C=206227	—				
		CUSTOMER DRAWING			SCALE	2:1	SHEET	1 of 1	REV	P