




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
K		REVISED PER ECR-26-286663	30JUL2026	GSK	CAS

NOTES:


1. WILL ACCEPT (19) MULTIMATE SOCKET CONTACTS.
2. CONTACT CAVITIES IDENTIFIED BY CHARACTERS ON FRONT AND REAR FACES OF CONNECTOR.
3. 3.81[.150] MAX INSULATION DIAMETER.
4. 2.54[.100] MAX INSULATION DIAMETER.
5. MATERIALS:
HOUSING USED ON 211773-1, 211773-2, 211773-7: THERMOPLASTIC, BLACK
HOUSING USED ON 211773-8 : THERMOPLASTIC, BLACK
PERIPHERAL SEAL: NITRILE BUTADIENE RUBBER, BLACK
THREADED INSERTS: BRASS



211773-1, 211773-2, 211773-6, 211773-7 & 211773-8



211773-4



211773-5

—	NO	211773-8
4-40 THREADED INSERTS	NO	211773-7
OBSOLETE 4-40 THREADED INSERTS	YES	211773-6
OBSOLETE —	NO	211773-5
OBSOLETE —	NO	211773-4
ø3.81 [.150] HOLES	NO	211773-2
ø3.81 [.150] HOLES	NO	211773-1
MOUNTING FEATURES	PERIPHERAL SEAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. URICH 02/JAN/01	 TE Connectivity				
		CHK M. CHACO 02/JAN/01					
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD M. CHACO 02/JAN/01	NAME	RECEPTACLE HOUSING, REVERSE SEX, SERIES 1, SHELL SIZE 23, CPC —			
		PRODUCT SPEC					
	1 PLC ± — 2 PLC ± — 3 PLC ± 0.13[.005] 4 PLC ± — ANGLE'S ± — FINISH —	APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
		WEIGHT					
MATERIAL			A1	00779	 211773	—	
		CUSTOMER DRAWING		SCALE	1:1	SHEET 1 OF 1	REV K