

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C1	REVISED	01NOV2016	C.O	T.K

- ⚠

MATERIAL: BRASS
- ⚠





FINISH : BLACK Su-Ni OVER Ni.
- ⚠

KEY POSITION: TYPE N IS NORMAL POSITION.
- ⚠





OPTION KEY IS TYPE A (-2) AND TYPE B (-3).
- ⚠

"#" IS BODY No.


145°	TYPE N	1-2201481-1	⚠
270°	TYPE B	2174211-3	
215°	TYPE A	2174211-2	
145°	TYPE N	2174211-1	
⚠ DIM L	DESCRIPTION	PART NO.	



AS SHOWN 2174211-*



REFERENCE SCALE 2:1
2174211-*



AS SHOWN 1-2174211-1

1	-	-	-	19P PLUG ADAPTOR SHORT WITH O-RING	②
-	1	1	1	19P PLUG ADAPTOR WITH O-RING	②
-	1	-	-	19P BAYONET PLUG PIN SOCKET/SOLDER CUP CONT ASSY TYPE B	①
-	-	1	-	19P BAYONET PLUG PIN SOCKET/SOLDER CUP CONT ASSY TYPE A	①
1	-	-	1	19P BAYONET PLUG PIN SOCKET/SOLDER CUP CONT ASSY TYPE N	①
1-#-1	-3	-2	-1	DESCRIPTION	ITEM NO.

⚠	REVISION OF EACH ASSY NO. (WHEN BLANK, USE DRAWING REVISION)	
QTY REQ. PER ASSY	PARTS LIST	

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN	03FEB2012	 TE Connectivity		
			CHK	03FEB2012			
			APVD	03FEB2012	NAME NMSMC 19P BAYONET PLUG PIN SOCKET / SOLDER CUP CONNECTOR / KIT		
			T.SUGIYAMA				
DIMENSIONS: mm			TOLERANCES, UNLESS OTHERWISE SPECIFIED: ±0.1		PRODUCT SPEC 108-78938		
			1 PLG ±		APPLICATION SPEC 114-5503		
			2 PLG ±				
			3 PLG ±		SIZE		
			4 PLG ±				
MATERIAL			ANGLES ±		CAGE CODE		
			FINISH				
			WEIGHT		DRAWING NO		
			0.000000				
			CUSTOMER DRAWING		RESTRICTED TO		
					SCALE		
					SHEET		
					REV		
					C1		