





P	LTR	DESCRIPTION	DATE	DWN	APVD
	B2	PART STATUS CHANGE TO DISCONTINUNACE	16JUL2026	NS	PS



OBSOLETE	77.0	23	2-284510-3
OBSOLETE	73.5	22	2-284510-2
OBSOLETE	70.0	21	2-284510-1
OBSOLETE	66.5	20	2-284510-0
OBSOLETE	63.0	19	1-284510-9
OBSOLETE	59.5	18	1-284510-8
OBSOLETE	56.0	17	1-284510-7
OBSOLETE	52.5	16	1-284510-6
OBSOLETE	49.0	15	1-284510-5
OBSOLETE	45.5	14	1-284510-4
OBSOLETE	42.0	13	1-284510-3
	38.5	12	1-284510-2
OBSOLETE	35.0	11	1-284510-1
	31.5	10	1-284510-0
	28.0	9	284510-9
	24.5	8	284510-8
	21.0	7	284510-7
	17.5	6	284510-6
	14.0	5	284510-5
	10.5	4	284510-4
	7.0	3	284510-3
	3.5	2	284510-2
DIM A		NO OF POS	PART NUMBER



- 1 MATERIALS AND FINISH
HOUSING : PA 6.6, UL 94-V0, COLOR GREEN
CLAMP : BRASS, NICKEL PLATED
TERMINAL : BRASS, TIN PLATED
CONTACT SPRING : PHOSPHOR BRONZE, TIN PLATED
CLAMPING SCREW : M2, BRASS, NICKEL PLATED
- 2 FLANGES WITH M2.5 FIXING SCREWS
- 3 WIRE SIZE RANGE
14 - 30 AWG
- 4 NOT CUMULATIVE TOLERANCE



284510-3 AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E. ZANOLINI 06FEB2002	TE Connectivity TERMINAL BLOCK, PLUG WITH SCREW FLANGE 3.5mm PITCH		
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK E. ZANOLINI 06FEB2002			
		APVD D. BIEVENOUR 06FEB2002			
		PRODUCT SPEC 108-20166			
	0 PLC ±°	APPLICATION SPEC 114-20079	NAME	SIZE	CAGE CODE
	1 PLC ±.3	WEIGHT -	300779	A	284510
	2 PLC ±.25	CUSTOMER DRAWING			SCALE 3:1
	3 PLC ±°				SHEET 1 OF 1
MATERIAL	4 PLC ±°				REV B2
	ANGLES ±2				
	FINISH				