


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	G1	REVISED PER ECR-18-013940	04SEP2018	ED	RS



9.60 [.380]	3.15 [.124]	2.49 [.098]		9-413889-4
9.60 [.380]	4.55 [.179]	3.51 [.138]		9-413889-3
9.60 [.380]	3.86 [.152]	3.20 [.126]		9-413889-2
9.60 [.380]	4.55 [.179]	3.51 [.138]		9-413889-1
9.60 [.380]	3.86 [.152]	3.20 [.126]		9-413889-0
9.60 [.380]	4.55 [.179]	3.51 [.138]		3-413889-4
7.87 [.310]	3.15 [.124]	2.49 [.098]		3-413889-3
7.87 [.310]	4.55 [.179]	3.20 [.138]		3-413889-2
7.87 [.310]	3.86 [.152]	3.20 [.126]		3-413889-1
7.87 [.310]	3.15 [.124]	2.49 [.098]		3-413889-0
7.87 [.310]	4.55 [.179]	3.51 [.138]		2-413889-7
7.87 [.310]	3.86 [.152]	3.20 [.126]		2-413889-4
9.60 [.380]	3.86 [.152]	3.20 [.126]		2-413889-1
9.60 [.380]	3.86 [.152]	2.67 [.105]		2-413889-0
9.60 [.380]	3.15 [.124]	2.49 [.098]		1-413889-9
9.60 [.380]	4.55 [.179]	3.51 [.138]		1-413889-8
9.60 [.380]	3.86 [.152]	3.20 [.126]		1-413889-7
9.60 [.380]	3.86 [.152]	2.67 [.105]		1-413889-6
9.60 [.380]	3.15 [.124]	2.49 [.098]		1-413889-5
9.60 [.380]	4.55 [.179]	3.51 [.138]		1-413889-4
9.60 [.380]	3.86 [.152]	3.20 [.126]		1-413889-3
9.60 [.380]	3.86 [.152]	2.67 [.105]		1-413889-2
9.60 [.380]	3.15 [.124]	2.49 [.098]		413889-9
9.60 [.380]	4.55 [.179]	3.51 [.138]		413889-6
9.60 [.380]	3.86 [.152]	3.20 [.126]		413889-3

C	B	A	FINISH	PART NUMBER
---	---	---	--------	-------------

- COPPER ALLOY
- BRIGHT TIN-LEAD PLATE PER ASTM B 545 WITH SUPPLEMENTAL ANTI-FRETTING LUBRICANT.
- NICKEL PLATE.
- GOLD PLATE
- BLACK NICKEL PLATE.
- TIN PLATE PER ASTM B 545 WITH SUPPLEMENTAL ANTI-FRETTING LUBRICANT.

OBSOLETE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± 0.05 [.002]
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH SEE TABLE

DWN
M. O'BRINE
29OCT99

CHK
B. MOYER
29OCT99

APVD
B. MOYER
29OCT99

PRODUCT SPEC
—

APPLICATION SPEC
—

WEIGHT
0.000000

CUSTOMER DRAWING

TE Connectivity

NAME
FERRULE

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-413889

RESTRICTED TO
—

SCALE
10:1

SHEET
1 OF 1

REV
G1