



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT - By - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	AB	REVISED PER ECR-18-009787	24JUL2018	BDA	MD









1 ACCEPTS RECEPTACLE CONTACTS 1217378(#18-#22 AWG SINGLE WIRE), 1217094(#18-#14 AWG SINGLE WIRE) AND 1217095 (TWO #18'S OR TWO #16'S OR A #16 + #18 COMBINATION).

2 FRONT AND BACK VIEWS SHOW ONLY THE GRIPPERS. FOR KEYING AND POLARIZATION FEATURES, SEE SPECIAL FRONT VIEW.


△3 DFE SYMBOL

△4 PRELIMINARY - NOT FOR PRODUCTION

5 NOTE DELETED

△6 PRE-PRODUCTION - FASR REQUIRED

△7 GWEPT 750C NO FLAME



KEYING & POLARIZATION
CODING AND COMBINATIONS
SPECIAL FRONT VIEW

RAST CONFIGURATION	FINISH/COLOR	KEYING FEATURE	POLARIZATION FEATURES	PART NO.
02-B	NATURAL	1C	1A & 2B	△7 1-521204-7
02-E	NATURAL	2D	1A & 2B	△7 1-521204-6
02-A	NATURAL	1C,2D	1B & 2A	△7 1-521204-5
-	NATURAL	NONE	NONE	△7 1-521204-4
02-A	NATURAL	1C,2D	1B & 2A	△4 1-521204-2
02-A	NATURAL	1C,2D	1B & 2A	△7 1-521204-1
-	BLUE	1C,2D	1A,1B,2A,2B	△4 1-521204-0
02-C	BLUE	1C,2D	2A	△4 521204-9
02-K	BLUE	1C	1A & 2A	521204-8
02-B	BLUE	1C	1A & 2B	521204-7
02-A	BLUE	1C,2D	1B & 2A	521204-6
-	BLUE	NONE	NONE	521204-5
-	NATURAL	1D	1A & 2B	△4 521204-4
02-E	NATURAL	2D	1A & 2B	△6 521204-3
-	BLUE	1D	1A & 2B	521204-2
02-E	BLUE	2D	1A & 2B	521204-1

521204

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± -
2 PLC ± 0.25 [.010]
3 PLC ± -
4 PLC ± -
ANGLES ± -

MATERIAL NYLON △3
FINISH SEE TABLE

DWN JR RUTH 10/20/98
CHK MS FEHER 10/20/98
APVD J GILLESPIE 10/20/98
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT

TE Connectivity

NAME HOUSING, RECEPT, POSITIVE-LOCK, MKIII, 6.35 [.250] SERIES, 2 POSITION -

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-521204	-

CUSTOMER DRAWING | SCALE 4:1 | SHEET 1 OF 1 | REV AB