
DRAWING MADE IN THIRD ANGLE PROJECTION

3	2	1	5016	LOC DF	DIST BO

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION , 19 .

© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

P	F	ZONE	LTR	DESCRIPTION	DATE	APPROVED
✓	—		V	REDRAWN & REVISED PER ECN R-1951	9-27-85	RER LBL
✓	✓		W	OBSOLETED -3 & -7 PER R-2760	3-4-87	SDG SLB
✓	✓		Y	REV PER ECN DF-5920	11-25-92	JL MM
			Z	REV PER 0G3D-269-03 CT	5-03	DSE



1. REELED FOR USE WITH STANDARD APPLICATORS.
2. REELED FOR USE WITH HEAVY DUTY MINI-APPLICATORS.
3. PLATED WITH .000100 MIN SILVER PER QQ-S-365.
4. PLATED WITH .000015 MIN GOLD PER MIL-G-45204 IN THE LOCALIZED GOLD PLATE AREA, GOLD FLASH ON THE REMAINDER, OVER .000030 MIN NICKEL PER QQ-N-290.
5. PLATED WITH .000030 MIN GOLD PER MIL-G-45204 IN THE LOCALIZED GOLD PLATE AREA, GOLD FLASH ON THE REMAINDER, OVER .000030 MIN NICKEL PER QQ-N-290.
6. PLATED WITH .000050 MIN 93-7% TIN-LEAD ALLOY OVER .000030 MIN NICKEL PER QQ-N-290.
7. WIRE RANGE = 10 AWG.
8. INSULATION RANGE = .190 - .220 DIA.
9. PLATED TIN (NO LEAD) .000050 MIN. THK. PER ASTM-B-545 OVER NICKEL, .000030 MIN. THK. PER QQ-N-290.

TERMINAL LATCH COLOR	FINISH	L.P. ASS'Y P/N REF	STRIP ASS'Y P/N
BLACK	9	66259-5	1-66253-0 2
BLACK	9	66259-5	66253-9 1
NATURAL	3	66259-4	66253-8 2
BLACK	4	OBSOLETE	66253-7 2
BLACK	5	66259-2	66253-6 2
BLACK	6	66259-1	66253-5 2
NATURAL	3	66259-4	66253-4 1
BLACK	4	OBSOLETE	66253-3 1
BLACK	5	66259-2	66253-2 1
BLACK	6	66259-1	66253-1 1

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES.
TOLERANCES ON:
DECIMALS ±.010
ANGLES

MATERIAL: SEE CALLOUT

FINISH: SEE DASH NO

CONTRACT NO

DR Rick Rohrbaugh 9-27-85

CHK Larry G. Lawver 10-1-85

APPD S. L. Blash 10-1-85

APPD Dennis E. Smith 10-3-85

DSGN APPD

OTHER APPD

AMP | AMP INCORPORATED Harrisburg, Pa. 17105

NAME: MALE TYPE XII CONTACT STRIP ASSEMBLY

SIZE	FSCM NO	DRAWING NO
C	00779	66253

SCALE NTS SHEET

66253

CUSTOMER DRAWING

AMP 1471-6 REV 2-81