


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	PART STATUS CHANGE TO DISCONTINUNACE	24JUN2026	NS	PS


MATERIALS AND FINISH:
HOUSING: PA 6-6, UL94V-0, COLOR: GREEN.
CLAMP: BRASS, NICKEL PLATED.
CONTACT SPRING: PHOSPHOR BRONZE, TIN PLATED.
CLAMPING SCREW: M2, BRASS, NICKEL PLATED.

ELECTRICAL:
VOLTAGE RATING: 300V
CURRENT RATING: 11A
WIRE SIZE RANGE: 14-30 AWG



ENVIRONMENTAL:
OPERATING TEMP RANGE: -40°C TO +110°C



CLAMPING SCREW



WIRE ENTRY



MATING FACE

OBSOLETE	56.0	16	1-1986371-6
	52.5	15	1-1986371-5
	49.0	14	1-1986371-4
	45.5	13	1-1986371-3
	42.0	12	1-1986371-2
	38.5	11	1-1986371-1
	35.0	10	1-1986371-0
	31.5	9	1986371-9
	28.0	8	1986371-8
	24.5	7	1986371-7
	21.0	6	1986371-6
	17.5	5	1986371-5
	14.0	4	1986371-4
	10.5	3	1986371-3
	7.0	2	1986371-2
	DIM L	NO OF POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL 18MAR2008	TE Connectivity		
DIMENSIONS: mm		CHK C RICHARD 3/19/08			
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± 0.3 2 PLC ± 0.25 3 PLC ± - 4 PLC ± - ANGLES ± 2°	APVD C RICHARD 3/19/08	NAME TERMINAL BLOCK, PLUG, VERTICAL STACKING LEFT HAND, 3.50mm PITCH		
		PRODUCT SPEC -	APPLICATION SPEC -		
MATERIAL -	FINISH -	WEIGHT 0.000000	SIZE A3	CAGE CODE 00779	DRAWING NO C-1986371
CUSTOMER DRAWING			SCALE NTS	SHEET 1 OF 1	REV A1