









REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
K		PCN-25-266602	08AUG2026	GSK	CAS



1 CONTACT CAVITIES IDENTIFIED BY CHARACTERS ON FRONT AND REAR FACE OF CONNECTOR.

△ -1, -2 AND -3 CONNECTORS WILL ACCEPT SEVEN (7) TYPE XII SOCKET CONTACTS.

△ -4 CONNECTOR WILL ACCEPT SIX (6) POWER BAND SOCKET CONTACTS AND THREE (3) TYPE III+ SIGNAL SOCKET CONTACTS.

△3	OBSOLETE	206136-4
△2		206136-3
△2	OBSOLETE	206136-2
△2		206136-1

PART
NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.RIDGLEY BG 7/30/90	TE Connectivity	
DIMENSIONS: INCHES		CHK R.STONE 04/26/91		
		APVD -	NAME	
		PRODUCT SPEC 108-10024	PLUG ASSEMBLY, SHELL SIZE 23, STANDARD SEX, CPC	
MATERIAL SEE CALLOUT		FINISH -	WEIGHT	RESTRICTED TO
			SIZE A2	
			CAGE CODE 00779	
			DRAWING NO C-206136	
			SCALE NTS	
			SHEET 1 OF 1	
			REV K	