


© – TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	S	REVISED PER ECR-26-286663	29JUL2026	GSK	CAS









RECOMMENDED PANEL CUTOUT

DETAIL A





DETAIL B

1. CAVITY IDENTIFICATION ON FRONT AND REAR FACE.
2. RECEPTACLE WILL ACCEPT NINE (9) MULTIMATE PIN CONTACTS.
3. WHITE DOT OVER MAJOR KEY, APPROX WHERE SHOWN.
4. OBSOLETE PART NUMBER.
5. MATERIALS
   HOUSING: THERMOPLASTIC, BLACK
   PERIPHERAL SEAL: NITRILE BUTADIENE RUBBER, BLACK
   THREADED INSERTS: BRASS
6. TE LOGO AND PART NUMBER LOCATED ON ANY FLANGE EDGE

4	MOUNTING FEATURE	NOTES	PERIPHERAL SEAL	SEE DETAIL	PART NUMBER
4	#4-40 THREADED INSERTS		NO	A	206705-7
4	Ø3.18 (.125) HOLES	3	NO	A	206705-5
	Ø3.18 (.125) HOLES	–	YES	B	206705-4
		–	YES	A	206705-3
		–	NO	B	206705-2
		–	NO	A	206705-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: MM [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± –
2 PLC ± 0.13 [.005]
3 PLC ± –
4 PLC ± –
ANGLES ± –

MATERIAL 5

FINISH –

DWN D.HARDY 05/19/94
CHK R.STONE 05/20/94
APVD – –
PRODUCT SPEC 108-10024
APPLICATION SPEC –
WEIGHT

TE Connectivity

NAME
RECEPTACLE HOUSING, STANDARD
SEX, SHELL SIZE 13, CPC
–

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-206705	–

CUSTOMER DRAWING | SCALE 2:1 | SHEET 1 OF 1 | REV S

206705