




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
J		PCN-25-266602	10AUG2026	GSK	CAS



- 1 .000100 MIN. MATTE TIN-LEAD OVER .000050 MIN NICKEL.
- 2 .000100 MIN. MATTE TIN OVER .000050 MIN NICKEL.

	6.53 [.257]	YES	NO	2	207890-5
OBSOLETE	4.04 [.159]	NO	YES	2	207890-3
	4.04 [.159]	NO	NO	2	207890-2
OBSOLETE	4.04 [.159]	NO	NO	1	207890-1
	DIM A	4-40 THREADED INSERTS	PERIPHERAL SEAL	FINISH	PART NUMBER

RECOMMENDED P.C. BOARD LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	0.13[.005]
3 PLC	±	-
4 PLC	±	-
ANGLES	±	-

MATERIAL SEE CALLOUT

FINISH SEE CALLOUT

DWN C.J.REIFSNYDER 05/15/95

CHK R.STONE 05/24/95

APVD AL FRANTUM 05/25/95

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE Connectivity

RECEPTACLE ASSEMBLY, POSTED, REVERSE SEX, SERIES 1, 23-37, CPC

SIZE A2 CAGE CODE 00779 DRAWING NO C-207890

RESTRICTED TO -

SCALE 2:1 SHEET 1 OF 1 REV J