


© – TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	M	REVISED PER ECR-26-286663	30JUL2026	MA	CAS







RECOMMENDED PANEL CUTOUT

	T	4-40 THREADED INSERTS	PERIPHERAL SEAL	MAX WIRE INSULATION DIA	PART NUMBER
	3.35±0.25 [.132±.010]	NO	NO	3.81 [.150]	211401-8
OBSOLETE	1.83±0.25 [.072±.010]	NO	NO	3.81 [.150]	211401-6
5	1.83±0.25 [.072±.010]	YES	NO	2.54 [.100]	211401-5
	1.83±0.25 [.072±.010]	YES	NO	3.81 [.150]	211401-4
	1.83±0.25 [.072±.010]	NO	YES	3.81 [.150]	211401-3
	1.83±0.25 [.072±.010]	NO	NO	2.54 [.100]	211401-2
	1.83±0.25 [.072±.010]	NO	NO	3.81 [.150]	211401-1

1. HOUNSING: THERMOPLASTIC, BLACK.
   PERIPHERAL SEAL: ELASTOMER, BLACK.
   THREADED INSERTS: BRASS.
2. CAVITY IDENTIFICATION ON FRONT AND REAR FACE.
3. WILL ACCEPT SEVEN (7) MULTIMATE PIN CONTACTS.
4. .0050MAX FLASH PERMITTED IN THE AREA OF DIMENSION T, .020 MAX FLASH PERMITTED ON MATING FACE SIDE AND .025 MAX FLASH PERMITTED ON REAR FACE SIDE.
5. PRELIMINARY PART NUMBER.
6. TE LOGO AND PART NUMBER LOCATED ON ANY FLANGE EDGE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± –
2 PLC ± 0.13 [.005]
3 PLC ± –
4 PLC ± –
ANGLES ± –

MATERIAL – 1

FINISH –

DWN D.HARDY 08-01-94
CHK R.STONE 08-10-94
APVD – —
PRODUCT SPEC —
APPLICATION SPEC —
WEIGHT

TE Connectivity Ltd.

NAME
RECEPTACLE HOUSING,
STANDARD SEX, 13-7, CPC
–


SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-211401	—


CUSTOMER DRAWING | SCALE 2:1 | SHEET 1 OF 2 | REV M

211401

© – TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	–	SEE SHEET 1	–	—	—





1. HOUNSING: THERMOPLASTIC, BLACK.
   PERIPHERAL SEAL: ELASTOMER, BLACK.
   THREADED INSERTS: BRASS.
2. CAVITY IDENTIFICATION ON FRONT AND REAR FACE.
3. WILL ACCEPT SEVEN (7) MULTIMATE PIN CONTACTS.
4. .005 MAX FLASH PERMITTED IN THE AREA OF DIMENSION T, .020 MAX FLASH PERMITTED ON MATING FACE SIDE AND .025 MAX FLASH PERMITTED ON REAR FACE SIDE.
6. TE LOGO AND PART NUMBER LOCATED ON ANY FLANGE EDGE

1.83±0.25 [.072±.010]	NO	2.54 [.100]	211401–7
T	PERIPHERAL SEAL	MAX WIRE INSULATION DIA	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.HARDY 08–01–94	TE Connectivity Ltd.
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± – 1 PLC ± – 2 PLC ± 0.13 [.005] 3 PLC ± – 4 PLC ± – ANGLES ± –	CHK R.STONE 08–10–94	NAME RECEPTACLE HOUSING, STANDARD SEX, 13–7, CPC
		APVD –	
		PRODUCT SPEC —	
		APPLICATION SPEC —	SIZE A2 / CAGE CODE 00779 / DRAWING NO C-211401 / RESTRICTED TO —
MATERIAL 1	FINISH –	WEIGHT	
		CUSTOMER DRAWING	SCALE 2:1 / SHEET 2 OF 2 / REV M