






P	LTR	DESCRIPTION	DATE	DWN	APVD
	D4	PART STATUS CHANGE TO DISCONTINUNACE	15JUL2026	NS	PS



282825-3 AS SHOWN



RECOMMENDED PC BOARD LAYOUT

1. MATERIALS AND FINISH)
HOUSING: PA 6-6, UL 94-V0, COLOR GREEN.
TERMINAL: COPPER ALLOY, FINISH: SEE TABLE.
2. SUITABLE FOR 1,6-2,4mm PC BOARD THICKNESS.
3. END-TO-END STACKABLE WITHOUT LOSS OF
CENTERLINE SPACING.
4. RECOGNIZED UNDER THE COMPONENT PROGRAM OF
UNDERWRITERS LABORATORIES INC. FILE N°E60677.
5. IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY
WITH IEC 998-1/998-2-1.
6. NOT CUMULATIVE TOLERANCE.

OBSOLETE	.000008 GOLD OVER NICKEL	9.68	2	2-282825-6
OBSOLETE	TIN PLATED	126.52	25	2-282825-5
	TIN PLATED	121.44	24	2-282825-4
OBSOLETE	TIN PLATED	116.36	23	2-282825-3
OBSOLETE	TIN PLATED	111.28	22	2-282825-2
OBSOLETE	TIN PLATED	106.20	21	2-282825-1
OBSOLETE	TIN PLATED	101.12	20	2-282825-0
OBSOLETE	TIN PLATED	96.04	19	1-282825-9
OBSOLETE	TIN PLATED	90.96	18	1-282825-8
OBSOLETE	TIN PLATED	85.88	17	1-282825-7
	TIN PLATED	80.80	16	1-282825-6
OBSOLETE	TIN PLATED	75.72	15	1-282825-5
	TIN PLATED	70.64	14	1-282825-4
OBSOLETE	TIN PLATED	65.56	13	1-282825-3
	TIN PLATED	60.48	12	1-282825-2
	TIN PLATED	55.40	11	1-282825-1
	TIN PLATED	50.32	10	1-282825-0
	TIN PLATED	45.24	9	282825-9
	TIN PLATED	40.16	8	282825-8
	TIN PLATED	35.08	7	282825-7
	TIN PLATED	30.00	6	282825-6
	TIN PLATED	24.92	5	282825-5
	TIN PLATED	19.84	4	282825-4
	TIN PLATED	14.76	3	282825-3
	TIN PLATED	9.68	2	282825-2
	TERMINAL FINISH	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 30 JUL 2001 F. ZANOLINI CHR 30 JUL 2001 D. BIEVENOUR APVD 30 JUL 2001 D. BIEVENOUR		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.3 1 PLC ±.3 2 PLC ±.25 3 PLC ±.25 4 PLC ±.3 ANGLES ±2 FINISH		NAME TERMINAL BLOCK HEADER ASSEMBLY 180 DEG OPEN ENDS, STACKING 5.08mm PITCH	
		PRODUCT SPEC 108-20166 APPLICATION SPEC 114-20079		SIZE A2	
MATERIAL 		WEIGHT -		CAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO C-282825	
				RESTRICTED TO -	
				SCALE 3:1 SHEET OF REV D4	