

© - TE Connectivity. All Rights Reserved.				REVISIONS				
P	LTR	DESCRIPTION			DATE	DWN	APVD	
	E	REVISED PER ECR-26-282233			01JUL2026	GSK	MP	


AMP

WIRE RANGE

4 AWG
STRANDED

METRIC

DIMENSIONS LISTED IN mm [INCHES]



1. TONGUE MATERIAL THK 1.22 ± 0.08 [.048±.003]
FOR 9.70 [.382] MAX INS DIA

- △2 MATERIAL:
BODY – COPPER PER ASTM B152
INSULATION – NYLON
- △3 FINISH:
BODY – TIN PLATE .000100 [0.00254]
MIN EXT PER ASTM B545
INSULATION – YELLOW

#10	5.00 ± 0.08 [.197±.003]	-	LOOSE PC	1-331456-0
#8	4.43 ± 0.08 [.171±.003]	-		331456
"B"	"A"	QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 105° c		THIS DRAWING IS A CONTROLLED DOCUMENT.			 TE Connectivity				
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: -		DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.20 [.008] 3 PLC ± - 4 PLC ± - ANGLES ± -	NAME TERMINAL, RING TONGUE, TERMINYL WIRE SIZE: 4 AWG					
	FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111					CIRCULAR MIL AREA: 16.8-26.7mm² [33,100-52,600] STRANDED	PRODUCT SPEC 108-162357	APPLICATION SPEC -	SIZE A3	CAGE CODE 00779	DRAWING NO C-331456
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.			MATERIAL 	FINISH 	CUSTOMER DRAWING			SCALE NTS	SHEET 1 OF 1	REV E