


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT - By - ALL RIGHTS RESERVED.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	AA1	REVISED PER ECR-19-003911	12MAR2019	BH	E.W






VIEW A-A
SCALE 8:1





SECTION B-B
SCALE 8:1



SECTION C-C
SCALE 8:1

8 CUT-OFF OFFSET IS ALLOWED BY 0.3mm MAX. THIS MAY BE REQUIRED FOR MANUFACTURING, BUT WILL NOT IMPACT THE INTENDED PERFORMACNE OF THE CONTACT.

1 DIMENSIONS IN BRACKETS ARE IN INCHES

2 CONTINUOUS STRIP ON REELS

3 FOREIGN PRODUCTION ONLY

4 FOREIGN PRODUCTION ONLY, INTERLEAVING PAPER REQUIRED

5 REELED UPSIDE DOWN WITH INTERLEAVING PAPER.

6 PRELIMINARY - NOT FOR PRODUCTION

7 FOR AMP ITALY ONLY, NOT STRESS RELIEVED.

2.29-3.30 [.090-.130]	0.3-0.8mm² [22-18]	±0.025 ±.001 0.81 [.032]	7 1-41772-1 6 5 41772-4 4 41772-3 3 41772-1 41772
INSUL RANGE	WIRE SIZE	MATING TAB THK	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± 0.25 [.010]
4 PLC ± -
ANGLES ± -

MATERIAL: BRASS
FINISH: TIN

DWN	JR RUTH	4/26/89
CHK	MS FEHER	4/26/89
APVD	C MEYERS	4/26/89
PRODUCT SPEC	-	
APPLICATION SPEC	114-2036	
WEIGHT	0	

TE Connectivity Ltd.

NAME: RECEPTACLE, FASTON,TM .250 SERIES -

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-41772	-

CUSTOMER DRAWING | SCALE 5:1 | SHEET 1 OF 1 | REV AA1