




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW RELEASE PER ECO-14-013594	09-05-14	DM	DM




SECTION A-A



Backshell

Compression Nut

6. PART NO. M902-2163
5. CABLE STRIPPED LENGTH: 63.50 [2.500] MAX.
4. CABLE SIZE: Ø.430 - Ø.570
3. TEMPERATURE RATING: -40°C TO +134°C [-40°F TO +273°F]
2. THIS PART IS USED WITH:
COMPRESSION NUT, M902-2053
1. THIS PART IS USED ON
HD1X-6-96X PLUG / RECEPTACLES
HD1X-6-12X PLUG / RECEPTACLES
SEE INVIDUAL CUSTOMER DRAWINGS

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. MEYER 05SEP2014		TE Connectivity											
		CHK I. GRANTCHAROVA 05SEP2014													
DIMENSIONS: MM [INCH]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± .63 [.025] 3 PLC ± 4 PLC ± ANGLES ± 5°		NAME BACKSHELL, SIZE 6 CABLE SIZE: Ø.430 - Ø.570 HD10 SERIES											
				APVD D. MEYER 05SEP2014											
				PRODUCT SPEC											
				APPLICATION SPEC											
MATERIAL PC/PBT		FINISH BLACK		SIZE A 3		CAGE CODE 4AFU8		DRAWING NO C- M902-2163		RESTRICTED TO -					
				WEIGHT 20.50 g											
				Customer Drawing						SCALE NONE		SHEET 1 OF 1		REV A	